



THIS DRAWING IS UNPUBLISHED.



RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
AD	00		E	EC 0G3C 0699 04	24NOV04	BSV
						DLS




- 0.00076 $[\pm 0.000030]$ GOLD IN LOCALIZED PLATE AREA
0.00381 $[\pm 0.000150]$ TIN ON SOLDER TAILS
ALL OVER 0.00127 $[\pm 0.000050]$ NICKEL
- IF PLANNING TO USE MORE THAN ONE MATING PAIR OF CONNECTORS TO INTERCONNECT 2 BOARDS, PLEASE REFER TO PARA. 3.3 IN THE APPLICATION SPEC, #114-7010
- KAPTON VACUUM PICK-UP BUTTON (SHOWN IN PHANTOM TO SHOW CONNECTOR DETAIL) $.236 \pm .005$ DIAMETER LOCATED $\phi .039$ Z Y
- PACKAGED IN TAPE AND REEL PER EIA-481 SPECIFICATIONS, SEE CHART FOR TAPE WIDTHS.
- HOUSING: LCP, COLOR:BLACK.
CONTACT: COPPER ALLOY PER ASTM SPECIFICATION B422.
HOLDDOWN: COPPER ALLOY PER ASTM SPECIFICATION B194.
- 0.00076 $[\pm 0.000030]$ GOLD IN LOCALIZED PLATE AREA,
0.00381 $[\pm 0.000150]$ TIN ON SOLDER TAILS, ALL OVER
0.00127 $[\pm 0.000050]$ NICKEL.



BASIC DIMENSIONS FOR
EVEN NO OF SPACES
(SEE TABLE)

BASIC DIMENSIONS FOR
ODD NO OF SPACES
(SEE TABLE)



RECOMMENDED BOARD LAYOUT
SCALE 5:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. SMITH 30 MAR 99	tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608			
DIMENSIONS: mm [INCHES]		CHK D. SIMPSON 30 MAR 99				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D.L. SIMPSON 30 MAR 99	NAME ASSEMBLY, RECEPTACLE, VERTICAL, DOUBLE ROW, SURFACE MOUNT, AMPMODU 50/50 GRID CONNECTOR			
0 PLC $\pm$ - 1 PLC $\pm$ - 2 PLC $\pm$ - 3 PLC $\pm$.005 4 PLC $\pm$ - ANGLES $\pm$ - FINISH		PRODUCT SPEC APPLICATION SPEC WEIGHT CUSTOMER DRAWING	SIZE A2	CAGE CODE 00779	DRAWING NO C=147120	RESTRICTED TO -
SCALE 10:1		SHEET 1 OF 1	REV E			