




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GE	00		S	REV PER ECO-12-013239	07JUL2012	RGV	DCS
			T	REV PER ECO-17-005979	27APR2017	JM	DS



1. PLATE OVER ALL WITH .000050 MIN NICKEL, THEN STRIPE MATING AREA WITH .000030 MIN GOLD, THEN GOLD FLASH OVERALL.
2. WIRE RANGE:18-16 AWG.
3. INSULATION RANGE: .098-.120 DIA.
4. DIE FEED: .450±.003.
5. CONTACT SUPPLIED ON REELS FOR MINI-APPLICATOR.
6. CUMMINS ELECTRONICS MUST BE INFORMED BY WAY OF A PRODUCT CHANGED IDENTIFICATION OF ALL CHANGES TO THE TE CUSTOMER DRAWINGS.
7. RECOMMENDED MATING PIN DIAMETER IS .040±.001 AS USED ON 212241 ASSEMBLY.

LOOSE PIECE OF 66773-2	66773-3
AS SHOWN	66773-2
MATERIAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
inch

MATERIAL
COPPER ALLOY

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±-

2 PLC ±-

3 PLC ±.005

4 PLC ±-

ANGLES ±-

FINISH

DWN
R. VESTAL
29 JUN 2012

CHK
D. STRAUSSER
29 JUN 2012

APVD
D. STRAUSSER
29 JUN 2012

PRODUCT SPEC
-

APPLICATION SPEC
114-2125

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
SOCKET CONTACT, ECMSC

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-66773

RESTRICTED TO
-

SCALE
5:1

SHEET
1

OF
1

REV
T