




- 1 MATERIAL:
SMOOTHBORE SMPM CONNECTOR BODY & CENTER CONTACT - BERYLLIUM COPPER,
ALLOY UNS C17300 CONDITION TDO4, PER ASTM B196
INSULATORS - TEFLON (PTFE) ROD, PER ASTM D 1710
MODULE BODY - STAINLESS STEEL, PER UNS 30300
SLOTTED SPRING PIN - NICKEL STAINLESS STEEL
- 2 FINISH:
MODULE BODY, CONNECTOR BODIES AND CENTER CONTACTS - GOLD PLATE OVER NICKEL
SLOTTED SPRING PIN - PASSIVATED
- 3 FINISH:
MODULE BODY, OSMM CONNECTOR & SLOTTED SPRING PIN - PASSIVATED
SMOOTHBORE SMPM CONNECTOR BODY & CENTER CONTACT - GOLD PLATED OVER NICKEL
- 4 SMPM MALE SMOOTH BORE INTERFACE PER MIL-STD-348, EXCEPT AS NOTED

LOC		DIST		REVISIONS					
-	-	P	LTR	DESCRIPTION	DATE	DWN	APVD		
		G		RELEASED PER ECO 11-025271	2-21-12	CT	WM		
		H		REVISED PER ECO-15-011822	24NOV2015	RS	CT		

OBSOLETE	3	2101510-2
	2	2101510-1
	SURFACE FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.T Morley 19AUG2009	 TE Connectivity		
		CHK S.T Morley 19AUG2009			
DIMENSIONS: [INCHES[mm]]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME 4 POSITION P.C.B. MOUNT R.F. MODULE SMPM SMOOTH BORE (M) TO OSMM (F) VITA 67, BACKPLANE	
		0 PLC ±	+	PRODUCT SPEC	
		1 PLC ±	+	APPLICATION SPEC	
MATERIAL		2 PLC ±	+	SIZE	
		3 PLC ±	+	CAGE CODE	
		4 PLC ±	+	DRAWING NO.	
		ANGLES	+	A100779	
		FINISH	+	C=2101510	
		SEE TABLE		RESTRICTED TO	
		WEIGHT		-	
		CUSTOMER DRAWING		CUSTOMER DRAWING	
		SCALE		8:1	SHEET 1 OF 1 REV H