




PRODUCT NO.	NOTE
72325-001	5.0V
72325-001LF	5.0V
72325-101	3.3V
72325-101LF	3.3V



NOTES:

- HEADER ASSY**
PLASTIC: HOUSING - HIGH TEMPERATURE THERMOPLASTIC UL94V-0 BLACK - ABOVE PCB
PIN: PHOSPHOR BRONZE
GUIDE MECHANISM ASSY
PLASTIC: GUIDE - HIGH TEMPERATURE THERMOPLASTIC UL94V-0 BLACK
COVER PLATE: STAINLESS STEEL
EMI CONTACT: PHOSPHOR BRONZE
- FINISH - PIN**
UNDER PLATING: 0.5um Ni
CONTACT AREA: 0.076 μm MIN. GOLD
SOLDER TAIL(TIN LEAD OPTION): 2.5um Sn-Pb
SOLDER TAIL(LEAD FREE OPTION): 2.5um PURE TIN
- DIM "L"**




4.25 $\pm$ 1	3.5 $\pm$ 1	5.0 $\pm$ 1
OTHERS	36,67	1,17,34,35,51,68
- RECOMMENDED HOLD DOWN - 2mm SCREWS**
95121 AND 2mm NUTS 92869.
SEE FOR CHARTED INFORMATION.
RECOMMENDED SCREW TORQUE: 1.0 TO 1.5 MAX in-lbs. (1.2-1.7 cm-kgs).
- SEE TA-1052 FOR PCB LAYOUT.
- MATING CONNECTOR: 91931-31169.** MUST BE PURCHASED SEPARATELY.
- IF LEAD FREE P.N.THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.00MM MINIMUM THICK CIRCUIT BOARD.
- IF LEAD FREE P/N.THE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
- LEAD FREE P/N PACKAGING MEETS GS-14-920 SPECIFICATION
- PRODUCT SPEC:110-263



mat'l. code				surface	tolerance	projection	product family			
ISO1302				ISO1101	ISO406		MCS			
l	tr	ec	n	odr	date	angle	title			
F	V05-0302	WB	04/21/05			0.X $\pm$ 0.3	EJECTOR HEADER ASSEMBLY			
G	N05-0116	WB	04/27/05			0.XX $\pm$ 0.13	68 POS. SMT TYPE 123			
H	EX-N-011412	ZK	04/02/12	0'±2'		0.XXX $\pm$ 0.051	scale 1:1			
				dr	R.GRAPE	8/16/96	dwg no			
				engr	D.BRANN	8/16/96	sheet 1 of 5			
				chr	D.BRANN	8/16/96	72325			
				appd	D.BRANN	8/16/96	A4			
sheet	revision	H	H	H	H	H	type Product Customer Drawing			
index	sheet	1	2	3	4	5				





PRODUCT NO.	NOTE
72325-002	5.0V
72325-002LF	5.0V
72325-102	3.3V
72325-102LF	3.3V



mat'l. code		surface	tolerance	projection	product family
ISO1302		ISO1101	ISO406		MCS
tolerances unless otherwise specified		tolerances		title	
H		angle	0.X±0.3	MM	EJECTOR HEADER ASSEMBLY
		0°±2'	0.XX±0.13	scale 1:1	68 POS. SMT TYPE 123
		dr	R.GRAPE	8/16/96	dwg no
		enr	D.BRANN	8/16/96	sheet 2 of 5
		chr	D.BRANN	8/16/96	size
		app	D.BRANN	8/16/96	A4
sheet index		revision			type Product Customer Drawing
sheet		sheet			


Printed: Sep 12, 2013

PRODUCT NO.	NOTE
72325-004	5.0V
72325-004LF	5.0V
72325-104	3.3V
72325-104LF	3.3V





NOTE:

TA-1052, PAGE 3, FOR PCB LAYOUT.




mat'l. code	surface ISO1302	tolerance ISO1101 ISO406	projection MM	product family MCS
ltr ecn nodr date	tolerances unless otherwise specified	angle 0°±2'	scale 1:1	EJECTOR HEADER ASSEMBLY 68 POS. SMT TYPE 123
	dr R.GRAPE	8/16/96		dwg no 72325
	engr D.BRANN	8/16/96		sheet 4 of 5
	chr D.BRANN	8/16/96		size A4
	appd D.BRANN	8/16/96		type Product Customer Drawing
sheet index	revision sheet			

PRODUCT NO.	NOTE
72325-005	5.0V
72325-005LF	5.0V
72325-105	3.3V
72325-105LF	3.3V



NOTE:

TA-1052, PAGE 3, FOR PCB LAYOUT.



mat'l. code	surface ISO1302	tolerance ISO1101 ISO406	projection MM	product family MCS
ltr ecn nodr date	tolerances unless otherwise specified	angle 0°±2'	scale 1:1	title EJECTOR HEADER ASSEMBLY 68 POS. SMT TYPE 123
H	0.X±0.3	dr R.GRAPE 8/16/96	FCI	dwg no 72325
	0.XX±0.13	engr D.BRANN 8/16/96		sheet 5 of 5
	0.XXX±0.051	chr D.BRANN 8/16/96		size A4
		appd D.BRANN 8/16/96		type Product Customer Drawing
sheet index	revision sheet			