

**A****Pushbutton**

AP Series Industrial Pushbutton Switch

Features/Benefits

- IP67 sealed
- 1,000,000 life cycle
- Illumination / non-illumination
- Multiple colored caps
- Threaded or snap-in mounting
- Caps available separately
- RoHS compliant

Typical Applications

- Harsh environments
- Off-Road
- Industrial
- Medical
- Transportation
- Joystick control modules
- Gaming
- Military



Specifications

FUNCTION: SPST Momentary
CONTACT ARRANGEMENT: N.O.
MOUNTING TYPE:
Snap-in (no panel seal)
Threaded body (hex nut, lock washer, and panel seal gasket provided)
Torque spec for threaded body: Do not exceed 8-9 in-lbs (0.9-1.0 N.m)

Mechanical

OPERATING LIFE: 1,000,000 cycles
TOTAL TRAVEL: 2.1 ± 0.2 mm
OPERATING POINT 1.55 ± 0.25 mm
OVER TRAVEL: 0.6 min.
OPERATING FORCE: $4N \pm 1N$ standard configuration; other force
option $2N \pm 0.5N$
VIBRATION: 10-500 Hz 10g Max
SHOCK: 60g 11ms sawtooth wave

Electrical

CONTACT RATING:
200mA @ 24 V DC resistive (500,000 cycles)
100mA @ 50 V DC resistive (500,000 cycles)
400mA @ 32 V AC resistive (500,000 cycles)
125mA @ 125 V AC resistive (1,000,000 cycles)
DIELECTRIC STRENGTH: 1000 V AC min.
INSULATION RESISTANCE: $1 \text{ G } \Omega$ @ 500 VDC
INITIAL CONTACT RESISTANCE 50 m Ω max (without wire leads)
BOUNCE TIME: <5 ms

Materials

HOUSING: PBT
BASE: PBT
CAP: PBT
ACTUATOR:
Illuminated: Clear polycarbonate
Non-illuminated: PBT
INTERNAL SEAL: Silicone rubber
TERMINALS: Copper alloy, gold over silver plating
MOVABLE CONTACT: Copper alloy, gold over silver plating
TERMINAL SEAL: Epoxy
WIRE LEADS: UL1569 Black 22 AWG

Operating Environment

OPERATING TEMPERATURE: -40°C to 85°C (+105°C non-illuminated)
ESD PROTECTION: 20 KV min.

Process Environment

SEALING: IP67 for threaded body
IP65 for snap-in version (no panel seal)

NOTE: Specifications and materials listed above are for switches with standard options.
For information on specific and custom switches, please contact Customer Service.

Build-A-Switch

To order, simply select desired option from each category and place in the appropriate box.

Designation		Operating Force		Actuator Style		Actuator Color		Illumination		Termination		Bushing Style**		Terminal Seal		Contact Material	
AP AP Series		2 2 Newtons 4 4 Newtons		D Dome / Convex C Concave E Extended Dome N None		0 No Cap 2 Black 3 Red 4 Orange 5 Yellow 6 Green 7 Blue 9 Gray		00 No LED* 01 Super White 02 Bi-color; Red (Green) 03 Red 05 Amber 06 Green 07 Super Blue 08 Bi-color; Amber (Green)		Z Solder Lug W 12" Wire Leads 22 AWG C*** PC Terminals		S** Snap-in plastic T Threaded plastic		E Epoxy All models are epoxy sealed		B Gold	

Please contact Customer Service for additional colors and paint / laser etched button options.

** No panel seal option
*** PC terminals not available with illumination

Contact Customer Service for additional hardware options.




AP Series Industrial Pushbutton Switch




A

Pushbutton

STANDARD VIEW




OPERATING FORCE




OPTION CODE	OPERATING FORCE
2	2 N, 200 g
4	4 N, 400 g


ACTUATOR STYLE







D DOME / CONVEX



E EXTENDED DOME



C CONCAVE




ACTUATOR COLOR



OPTION CODE	ACTUATOR COLOR
0	No Cap
2	Black
3	Red
4	Orange
5	Yellow
6	Green
7	Blue
9	Gray

For additional colors please contact Customer Service.



Third Angle
Projection



12 Feb 14

A-111

Dimensions are shown: mm (inches)
Specifications and dimensions subject to change

www.ck-components.com

**A****Pushbutton**

AP Series Industrial Pushbutton Switch

ILLUMINATION



OPTION CODE	ILLUMINATION TYPE	TYPICAL INTENSITY*		PEAK WAVELENGTH	Vf Forward Voltage
		MIN	MAX		
		(mcd)		(nm)	
00	Model without illumination	N/A		N/A	
01	LED Super White	4,000	5,000	N/A	3.5
02	LED Bi-Color – Red (Green)	10	20	635/565	2.0
03	LED Red	4	8	700	2.0
05	LED Amber	35	50	610	2.0
06	LED Green	35	50	565	2.0
07	LED Super Blue	800	1,500	470	3.8
08	LED Bi-Color – Amber (Green)	10	10	585/565	2.0

*LED FORWARD CURRENT: 20 mA


LED FORWARD VOLTAGE: see chart above

LED REVERSE VOLTAGE: 5.0 V MAX

* For information on specific and custom LED, please contact Customer Service.

NOTE:



For bi-color LED's the polarity must be reversed to alternate the color





BUSHING STYLE




S SNAP-IN




T THREADED PLASTIC



PANEL CUTOUT



PANEL THICKNESS	DIM A (± 0.05 mm)	DIM B (± 0.05 mm)
1 mm [0.039 in]	13.70 mm [0.539 in]	13.00 mm [0.512 in]
2 mm [0.079 in]	13.80 mm [0.539 in]	13.00 mm [0.512 in]
3 mm [0.118 in]	13.90 mm [0.547 in]	13.10 mm [0.516 in]
THREADED BODY MIN PANEL THICKNESS 1 mm	13.70 mm [0.539 in]	13.00 mm [0.512 in]



12 Feb 14

A 0.1mm min. chamfer on the leading edge of the mounting hole is recommended for snap-in version.

Dimensions are shown: mm (inches)
Specifications and dimensions subject to change

AP Series Industrial Pushbutton Switch






A

Pushbutton

TERMINATION





Z SOLDER LUG







* Switching terminals are gold and LED terminals are silver

C PC TERMINALS


*** Illumination not available with PC Terminals



W 12" WIRE LEADS 22 AWG



Wires: Black wires - Terminals
Red wires - LED (+) Positive
White wire - LED (-) Negative





AP Series Industrial Pushbutton Switch

A

Pushbutton

CONTACT MATERIAL



B GOLD

OPTION CODE	CONTACT MATERIAL
B	Gold

TERMINAL SEAL




E EPOXY

All models are epoxy sealed

HARDWARE


LOCK WASHER

Part Number 647D00000




HEX NUT

Part number 515D00000



PANEL SEAL

Part Number 655D00000




Caps available on next page



12 Feb 14

A-114



Third Angle
Projection

Dimensions are shown: mm (inches)
Specifications and dimensions subject to change

www.ck-components.com

AP Series Industrial Pushbutton Switch



A

Pushbutton

AVAILABLE CAPS



481D XX XXX



Cap Color
Style

OPTION	CAP COLOR
01	WHITE
02	BLACK
03	RED
04	ORANGE
05	YELLOW
06	GREEN
07	BLUE
08	BROWN
09	GRAY

PART NUMBER	HOLE	STYLE
481DXX000	NO	DOME
481DXX001	YES	DOME
481DXX002	NO	EXTENDED DOME
481DXX003	YES	EXTENDED DOME
481DXX004	NO	CONCAVE
481DXX005	YES	CONCAVE



DOME

481DXX000 = NO HOLE
481DXX001 = HOLE





EXTENDED DOME

481DXX002 = NO HOLE
481DXX003 = HOLE




CONCAVE

481DXX004 = NO HOLE
481DXX005 = HOLE



12 Feb 14

A-115



Third Angle
Projection

Dimensions are shown: mm (inches)
Specifications and dimensions subject to change

www.ck-components.com