

10 nH Inductor (Top View)

ACCU-L[®] TECHNOLOGY

The Accu-L[®] SMD Inductor is based on thin-film multilayer technology. This technology provides a level of control on the electrical and physical characteristics of the component which gives consistent characteristics within a lot and lot-to-lot.

The original design provides small size, excellent high-frequency performance and rugged construction for reliable automatic assembly.

The Accu-L[®] inductor is particularly suited for the telecommunications industry where there is a continuing trend towards miniaturization and increasing frequencies. The Accu-L[®] inductor meets both the performance and tolerance requirements of present cellular frequencies 450MHz and 900MHz and of future frequencies, such as 1700MHz, 1900MHz and 2400MHz.

FEATURES

- High Q
- RF Power Capability
- High SRF
- Low DC Resistance
- Ultra-Tight Tolerance on Inductance
- Standard 0603 and 0805 Chip Size
- Low Profile
- Rugged Construction
- Taped and Reeled

APPLICATIONS

- Mobile Communications
- Satellite TV Receivers
- GPS
- Vehicle Locations Systems
- Filters
- Matching Networks

LGA High-Q RF Inductor

ITF TECHNOLOGY


The LGA Inductor is based on thin-film multilayer technology. The technology provides a miniature part with excellent high frequency performance and rugged construction for reliable automatic assembly.

APPLICATIONS

- Mobile Communications
- Satellite TV Receivers
- GPS
- Vehicle Location Systems
- Wireless LANs
- Filters
- Matching Networks

FEATURES

- Inherent Low Profile
- Self Alignment During Reflow
- Excellent Solderability
- Low Parasitics
- Better Heat Dissipation



	0402
L	1.0±0.10 (0.040±0.004)
W	0.58±0.07 (0.023±0.003)
T	0.35±0.10 (0.014±0.004)
A	0.48±0.05 (0.019±0.002)
B	0.17±0.05 (0.0067±0.002)
S,H	0.064±0.05 (0.0025±0.002)

HOW TO ORDER

L
Product
Inductor

0402
Size
0402

4R7
Inductance
Expressed in nH
Letter R denotes
Decimal Point
Example:
R68 = 0.68nH
4R7 = 4.7nH

D
Tolerance
L ≤ 1nH:
A = ±0.5nH
B = ±0.1nH
L ≤ 2.7nH:
A = ±0.5nH
B = ±0.1nH
C = ±0.2nH
D = ±0.5nH
L ≤ 6.8nH:
B = ±0.1nH
C = ±0.2nH
D = ±0.5nH

H
Specification
Code

L
Termination
Code
L = SnPb
N = Sn100
Lead Free

TR
Packaging
Code

QUALITY INSPECTION


Finished parts are 100% tested for electrical parameters and visual characteristics. Each production lot is evaluated on a sample basis for:

- Static Humidity: 85°C, 85% RH, 160 hours
- Endurance: 125°C, I_R, 4 hours

TERMINATION


Nickel/Solder coating compatible with automatic soldering technologies: reflow, wave soldering, vapor phase and manual.

Recommended Pad Layout Dimensions mm (inches)



0402

MARKING AND ORIENTATION IN TAPE (Top View)



0402

0402 ELECTRICAL SPECIFICATIONS TABLE

450MHz				900MHz	1900MHz	2400MHz	SRF min. (MHz)	R _{DC} max. (Ω)	I _{DC} max. (mA)
L(nH)	Tolerance A=±0.05nH, B=±0.1nH C=±0.2nH, D=±0.5nH	Q (min.)	Q (Typ)	Q (Typ)	Q (Typ)	Q (Typ)			
0.82	± 0.05nH, ± 0.1nH	25	40	50	60	70	20000	0.06	500
1.0	± 0.05nH, ± 0.1nH	20	30	35	40	50	20000	0.15	500
1.2	± 0.05nH, ± 0.1nH, ±0.2nH	20	30	30	40	45	20000	0.20	400
1.5	± 0.05nH, ± 0.1nH, ±0.2nH	20	25	30	40	40	18000	0.20	400
1.8	± 0.05nH, ± 0.1nH, ±0.2nH	18	20	30	35	40	16000	0.20	400
2.2	± 0.05nH, ± 0.1nH, ±0.2nH	15	20	25	35	40	15000	0.20	400
2.7	± 0.05nH, ± 0.1nH, ±0.2nH	15	20	25	35	40	9500	0.25	250
3.3	± 0.1nH, ± 0.2nH, ±0.5nH	15	20	25	35	40	8500	0.40	250
3.9	± 0.1nH, ± 0.2nH, ±0.5nH	13	20	20	30	30	8000	0.45	250
4.7	± 0.1nH, ± 0.2nH, ±0.5nH	13	20	20	30	30	7500	0.45	250
5.6	± 0.1nH, ± 0.2nH, ±0.5nH	13	20	20	30	30	7000	0.65	200
6.8	± 0.1nH, ± 0.2nH, ±0.5nH	12	15	20	25	30	6500	0.90	200