



Spiral Wrap T&B Catalog Number:

SRPE-250F-9-C

UPC Number:

72849411726

Status:

Active

Description:

Forward Cut Spiral Wrap Natural Polyethylene .250" OD, 100 Feet Per Roll

Features

Perfect for protection of bundles from .063 to 7 inch diameters.

Install with gaps for greater flexibility or butted together for maximum abrasion resistance, insulation, and rigidity.

Available in 3 materials.

General

Style	Forward Cut
Material	Polyethylene
Color	Natural

Dimension Information

Pitch (inches)	0.375
Nominal Wall Thickness (inches)	0.045
Max. Wire Bundle Diameter (inches)	2.000
Min. Wire Bundle Diameter (inches)	0.188
Outside Diameter (inches)	0.250

Specifications

Flammability Rating	UL 94 HB
---------------------	----------

Tooling

Application Tools	SR-100
-------------------	--------

Packaging

T&B Order Multiple	1
T&B Inner Pack	1
Package in Units	12
Feet per Roll	100
T&B Sold in UOM	Each
T&B Weight Per UOM	1.58 lbs. Each

Notes

Install with gaps for greater flexibility or butted together for maximum abrasion resistance, insulation and rigidity.

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com