




LOC	DIST	REVISIONS					
CM	53	P	LTR	DESCRIPTION	DATE	DWN	APVD
			DI	REVISED PER ECO-11-005027	16MAR2011	RK	HMR




- ① 0.000762 THK GOLD STRIPE IN THE GOLD PLATE AREA,
BRIGHT TIN IN THE CRIMP AREA, OVER NICKEL PLATE.
- ② 0.000381 THK GOLD STRIPE IN THE GOLD PLATE AREA,
BRIGHT TIN IN THE CRIMP AREA, OVER NICKEL PLATE.
- ③ 0.0015 - 0.0040 THK BRIGHT TIN.
4. WIRE RANGE: 26 - 30 AWG.
5. INSULATION RANGE 0.89 - 1.524.
- ⑦ 0.000762 THK GOLD STRIPE IN THE GOLD PLATE AREA,
BRIGHT TIN-LEAD IN THE CRIMP AREA, OVER NICKEL PLATE.
- ⑧ 0.000381 THK GOLD STRIPE IN THE GOLD PLATE AREA,
BRIGHT TIN-LEAD IN THE CRIMP AREA, OVER NICKEL PLATE.



SECTION C-C
SCALE 20:1




SECTION **B - B**
SCALE 20:1



SECTION **A - A**
SCALE 20:1

	1-794611-2
	1-794611-1
	794611-3
	794611-2
	794611-1
FINISH	PART NUMBER



3 DIMENSIONAL MODEL
SCALE 8:1



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 19-OCT-1999 CHR K. COBLE 19-OCT-1999 APVD K. COBLE 19-OCT-1999		 TE Connectivity		NUMBER	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±0.13 3 PLC ±- 4 PLC ±- ANGLES ±0.3° FINISH		NAME CONTACT, RECEPTACLE, CRIMP SNAP-IN, MICRO MATE-N-LOK(TM)		PRODUCT SPEC - APPLICATION SPEC - WEIGHT -	
MATERIAL 0.2 PH BRZ		SEE TABLE		SIZE A2		CAGE CODE 00779	
				DRAWING NO C-794611		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE		SHEET OF REV	