





Copyright FCI.


D

A

B

C



spec ref -				dr	Andrew Yong	2010/10/14	projection 	MM / INCH 	size	A3	scale	10:1	
tolerance std				eng	Andrew Yong	2011/08/22			ecn no				ELX-S-005192-1
ISO 406				chr	Aik-Peng Lim	2011/08/22			rel level				Released
ISO 1101				appr	Chen-Hong Tan	2011/08/22			product family				LPVCC
surface 	linear	0.X	±0.3/.01		title	LOW PROFILE VCC SMT			dwg no	92086		rev	V
		0.XX	±0.13/.005			4.0 ASSY WITH 0.46 LOCATING FEATURES							
		0.XXX	±0.051/.0020										
	ISO 1302	angular	0°	±2°	www.fci.com	cat. no.	-	Product - Customer Drw				sheet 1 of 3	

A	1		2	
	PRODUCT NO.	POSITIONS	DIM. A	DIM.B
	92086-X04	2 X 2	2.00 / .079	3.92 / .154
	-X06	2 X 3	4.00 / .158	5.92 / .233
	-X08	2 X 4	6.00 / .236	7.92 / .312
	-X10	2 X 5	8.00 / .315	9.92 / .391
	-X12	2 X 6	10.00 / .394	11.92 / .469
B	-X14	2 X 7	12.00 / .472	13.92 / .548
	-X16	2 X 8	14.00 / .551	15.92 / .627
	-X18	2 X 9	16.00 / .630	17.92 / .706
	-X20	2 X 10	18.00 / .709	19.92 / .784
	-X22	2 X 11	20.00 / .787	21.92 / .863
	-X24	2 X 12	22.00 / .866	23.92 / .942
	-X26	2 X 13	24.00 / .945	25.92 / 1.020
	-X28	2 X 14	26.00 / 1.024	27.92 / 1.099
	-X30	2 X 15	28.00 / 1.102	29.92 / 1.178

A	3		4	
	PRODUCT NO.	CONTACT AREA PLATING.	SOLDER TAIL PLATING.	
	92086-XXX	0 = 0.20µm/8µ" Au	TIN/LEAD	
		1 = 0.76µm/30µ" Au	TIN/LEAD	
		3 = 0.38m/15µ" Au	TIN/LEAD	
		6 = 0.76µm/30µ" PdNi WITH 0.076µm/3µ" Au FLASH (POST PLATED)		
	92086-XXXLF	0 = 0.20µm/8µ" Au	GOLD FLASH	
		1 = 0.76µm/30µ" Au	GOLD FLASH	
		3 = 0.38m/15µ" Au	GOLD FLASH	
		6 = 0.76µm/30µ" PdNi WITH 0.076µm/3µ" Au FLASH (POST PLATED)		





FIG. 1
NOTE 6 (b)



RECOMMENDED PAD LAYOUT

spec ref		-		dr		Andrew Yong		2010/10/14		projection		MM / INCH		size		A3		scale		10:1	
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng		Andrew Yong		2011/08/22						ecn no		ELX-S-005192-1					
chr				Aik-Peng Lim		2011/08/22		rel level						Released							
ISO 406 ISO 1101				appr		Chen-Hong Tan		2011/08/22						product family		LPVCC					
surface ISO 1302		linear		0.X		±0.3/.01				title		LOW PROFILE VCC SMT		dwg no		92086		rev		V	
				0.XX		±0.13/.005															
				0.XXX		±0.051/.0020															
angular		0°		±2°		www.fci.com		cat. no.		-		Product - Customer Drw		sheet 2 of 3							

A

- B

C

D