




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION ,19 .
© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.


LOC	DIST	P	F	REVISIONS			
				ZONE	LTR	DESCRIPTION	DATE
CM	53				C	REV & REDRAWN PER ECN CM-11	1-20-93
							K5 RS



1. 0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA AND ON INSIDE OF WIRE BARREL; 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
2. WIRE RANGE: 0.05-0.15mm² [30-26] AWG. INSULATION RANGE: 0.81-1.45[.032-.057] DIA.
3. DIMENSIONS IN BRACKETS ARE IN INCHES.



SECTION A-A
SCALE 10:1



SECTION B-B
SCALE 10:1

METRIC

		GOLD 1		0.30 [.012] PH BRZ		770012-6	
		FINISH		MATERIAL		PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN MM [INCHES] TOLERANCES ON: 2 PLC DEC ± _____ 3 PLC DEC ± _____ ANGLES ± _____		DR 4-1-93 K. SALMON		AMP		AMP INCORPORATED Harrisburg, Pa. 17105	
		CHK 4-1-93 R. SWING					
		APPD 4-1-93 M. TRULL		NAME SOCKET, UNIVERSAL MATE-N-LOK™ II			
		APPD 4-1-93 M. TRULL					
		PRODUCT SPEC _____					
MATERIAL SEE TABLE		APPLICATION SPEC _____		SIZE B	FSCM NO 00779	DRAWING NO 770012	
FINISH SEE TABLE		WEIGHT _____		SCALE 4:1		SHEET 1 OF 1	

CUSTOMER DRAWING