



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

CURRENT CAPACITY (AMPS)								
RESISTIVE DC VOLTS			LOAD AC VOLTS		LAMP LOAD		INDUCTIVE LOAD	
30	115	250	115	230	30 VDC	115 VAC	30 VDC	115 VAC
18	.75	.5	11	6	4	2	10	8




CIRCUIT MADE WITH TOGGLE LEVER IN		
KEYWAY SIDE	CENTER	OPPOSITE KEYWAY
MOMENTARY POSITION	MAINTAINED POSITION	MAINTAINED POSITION



NOTES

- ① FURNISHED UNASSEMBLED
- 2 - THIS SWITCH IS CAPABLE OF WITHSTANDING A TEMPERATURE OF 160°F CONTINUOUSLY AT FULL RATED LOAD
 - 3 - FOR TERMINAL COVER SEE MICRO SWITCH CATALOG LISTING 5PA9
 - 4 - CIRCUIT DESIGNATION & MICRO SWITCH CATALOG LISTING 4TL11-558E MARKED ON SIDE OF SWITCH

THIRD ANGLE PROJECTION



SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
ONE PLACE	(.0)	±.030
TWO PLACE	(.00)	±.015
THREE PLACE	(.000)	±.005
ANGLES		±

WEIGHT **95 GRAMS MAX**