



Ni-Zn

Ferrites for EMI Suppression

BB series(1 Hole)

---

**REMINDERS FOR USING THESE PRODUCTS**

Please be sure to read this manual thoroughly before using the products.

The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition.

The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property.

When using the products for specific purposes, please first make confirmations in areas such as safety, reliability, and quality.

Please understand that we are not in a position to be held responsible for any damage or the like caused by any use exceeding the range or conditions of this specification sheet or by any use in the specific applications.

- |                                                             |                                                                              |
|-------------------------------------------------------------|------------------------------------------------------------------------------|
| (1) Aerospace/Aviation equipment                            | (8) Public information-processing equipment                                  |
| (2) Transportation equipment (electric trains, ships, etc.) | (9) Military equipment                                                       |
| (3) Medical equipment                                       | (10) Electric heating apparatus, burning equipment                           |
| (4) Power-generation control equipment                      | (11) Disaster prevention/crime prevention equipment                          |
| (5) Atomic energy-related equipment                         | (12) Safety equipment                                                        |
| (6) Seabed equipment                                        | (13) Other applications that are not considered general-purpose applications |
| (7) Transportation control equipment                        |                                                                              |

When using this product in general-purpose standard applications, you are kindly requested to take into consideration securing protection circuit/equipment or providing backup circuits, etc to ensure higher safety.

# Ferrites for EMI Suppression

Product compatible with RoHS directive  
Halogen-free

## Overview of the BB Series

Bead cores series are easy to handle and are supplied in various materials, shapes and packaging styles to meet for users' requests.

### FEATURES

- Appropriate materials and shapes can be selected from various cores to suppress EMI effectively.

### APPLICATION

Imaging devices, audio equipment, automotive electronics, telecommunication devices, office automation equipment, and digital interface various other cables.

- Absorption EMI and penetrating noise
- Prevent parasitic oscillation

### PART NUMBER CONSTRUCTION

|          |            |                              |   |                      |   |                              |               |
|----------|------------|------------------------------|---|----------------------|---|------------------------------|---------------|
| HF30     | BB         | 1.8                          | × | 5                    | × | 0.7                          | □□□□          |
| Material | Core shape | Outer diameter dimensions(A) |   | Length dimensions(B) |   | Inner diameter dimensions(C) | Internal code |

### RANGE OF USE AND STORAGE TEMPERATURE

| Temperature range*            |                               |
|-------------------------------|-------------------------------|
| Operating temperature<br>(°C) | Storage temperature**<br>(°C) |
| −40 to +85                    | −40 to +85                    |

\* The temperature range has a different case by materials.

\*\* The Storage temperature range is for after the circuit board is mounted.

○ RoHS Directive Compliant Product: See the following for more details related to RoHS Directive compliant products. <http://www.tdk.co.jp/rohs/>


○ Halogen-free: Indicates that Cl content is less than 900ppm, Br content is less than 900ppm, and that the total Cl and Br content is less than 1500ppm.

• All specifications are subject to change without notice.

## Ni-Zn BB series



## SHAPES AND DIMENSIONS




|          |            |                              |   |                      |   |                              |               |
|----------|------------|------------------------------|---|----------------------|---|------------------------------|---------------|
| HF30     | BB         | 1.8                          | × | 5                    | × | 0.7                          | □□□□          |
| Material | Core shape | Outer diameter dimensions(A) |   | Length dimensions(B) |   | Inner diameter dimensions(C) | Internal code |

| Part No.          | Dimensions |             |          | Electrical characteristics   |        |
|-------------------|------------|-------------|----------|------------------------------|--------|
|                   | A<br>(mm)  | B           | C        | Impedance Z                  |        |
|                   |            |             |          | typ.<br>(Ω)<br>23°C<br>10MHz | 100MHz |
| HF30BB1.8X5X0.7   | 1.8±0.15   | 5.0±0.3     | 0.7±0.1  | 3.4                          | 36     |
| HF30BB2.5X2X0.8   | 2.5±0.15   | 2.0±0.2     | 0.8±0.1  | 1.9                          | 20     |
| HF30BB3X5X1       | 3.0±0.15   | 5.0±0.3     | 1.0±0.1  | 3.3                          | 37     |
| HF30BB3.5X5X1.3   | 3.5±0.15   | 5.0±0.3     | 1.3±0.1  | 3.2                          | 32     |
| HF30BB5X5X2       | 5.0±0.15   | 5.0±0.3     | 2.0±0.15 | 2.7                          | 33     |
| HF30BB6.4X5X3.2   | 6.4±0.2    | 5.0±0.2     | 3.2±0.15 | 2.6                          | 26     |
| HF40BB1.7X1.9X0.7 | 1.7±0.15   | 1.9±0.2     | 0.7±0.1  | 1.8                          | 16     |
| HF40BB3X5X1       | 3.0±0.15   | 5.0±0.3     | 1.0±0.1  | 9                            | 60     |
| HF40BB3.4X3X1     | 3.4±0.15   | 3.0±0.2     | 1.0±0.1  | 7                            | 39     |
| HF40BB3.5X5X1.3   | 3.5±0.15   | 5.0±0.3     | 1.3±0.1  | 9.1                          | 50     |
| HF40BB4.5X4X2.5-G | 4.5±0.15   | 4.0±0.2     | 2.5±0.15 | 4.5                          | 32     |
| HF40BB4.5X5X1.6   | 4.5±0.15   | 5.0±0.3     | 1.6±0.1  | 11                           | 60     |
| HF40BB5X5X2       | 5.0±0.15   | 5.0±0.3     | 2.0±0.15 | 9.4                          | 52     |
| HF40BB5X6X2.5     | 5.0±0.15   | 6.0±0.3     | 2.5±0.15 | 10                           | 50     |
| HF40BB5.5X5X2.5   | 5.5±0.2    | 5.0±0.3     | 2.5±0.15 | 8.1                          | 43     |
| HF40BB6X3.8X3A-G  | 6.0±0.2    | 3.8±0.2     | 3.0±0.2  | 4                            | 35     |
| HF57BB2.85X2X1.35 | 2.85±0.1   | 2.0±0.15    | 1.35±0.1 | 8                            | 23     |
| HF57BB2.85X5X1.35 | 2.85±0.1   | 5.0±0.2     | 1.35±0.1 | 20                           | 54     |
| HF57BB3.35X2X2    | 3.35±0.2   | 2.0±0.1     | 2.0±0.2  | 6                            | 20     |
| HF57BB3.5X1X1.6   | 3.5±0.15   | 1.0±0, -0.2 | 1.6±0.1  | 4.5                          | 17     |
| HF57BB3.5X1.5X1.3 | 3.5±0.15   | 1.5±0.15    | 1.3±0.1  | 9                            | 23     |
| HF57BB3.5X3X1.3   | 3.5±0.15   | 3.0±0.2     | 1.3±0.1  | 16                           | 40     |
| HF57BB3.5X5X1.3   | 3.5±0.15   | 5.0±0.3     | 1.3±0.1  | 28                           | 65     |
| HF57BB3.6X3.2X2.7 | 3.6±0.15   | 3.2±0.2     | 2.7±0.15 | 6                            | 17     |
| HF57BB4X2X2       | 4.0±0.15   | 2.0±0.15    | 2.0±0.15 | 8                            | 24     |
| HF57BB4X5X2       | 4.0±0.15   | 5.0±0.3     | 2.0±0.15 | 19                           | 46     |
| HF57BB4.5X4X2.5   | 4.5±0.15   | 4.0±0.2     | 2.5±0.15 | 14                           | 37     |
| HF57BB4.8X4.8X2.4 | 4.8±0.2    | 4.8±0.2     | 2.4±0.15 | 18                           | 49     |
| HF57BB5X5X2       | 5.0±0.15   | 5.0±0.3     | 2.0±0.15 | 25                           | 59     |

## Ni-Zn BB series



## SHAPES AND DIMENSIONS



|          |            |                              |   |                      |   |                              |               |
|----------|------------|------------------------------|---|----------------------|---|------------------------------|---------------|
| HF70     | BB         | 1.8                          | × | 5                    | × | 0.7                          | □□□□          |
| Material | Core shape | Outer diameter dimensions(A) |   | Length dimensions(B) |   | Inner diameter dimensions(C) | Internal code |


| Part No.           | Dimensions  |            |          | Electrical characteristics                  |        |
|--------------------|-------------|------------|----------|---------------------------------------------|--------|
|                    | A<br>(mm)   | B          | C        | Impedance Z<br>typ.<br>(Ω)<br>23°C<br>10MHz | 100MHz |
| HF70BB1.8X5X0.7    | 1.8±0.15    | 5.0±0.3    | 0.7±0.1  | 31                                          | 48     |
| HF70BB2.5X2.2X0.8  | 2.5±0.15    | 2.2±0.2    | 0.8±0.1  | 15                                          | 27     |
| HF70BB2.5X5X0.8    | 2.5±0.15    | 5.0±0.3    | 0.8±0.1  | 31                                          | 51     |
| HF70BB3X5X1        | 3.0±0.15    | 5.0±0.3    | 1.0±0.1  | 33                                          | 53     |
| HF70BB3.4X3X1      | 3.4±0.15    | 3.0±0.2    | 1.0±0.1  | 22                                          | 36     |
| HF70BB3.5X2X1.3    | 3.5±0.15    | 2.0±0.15   | 1.3±0.1  | 13                                          | 24     |
| HF70BB3.5X5X0.8    | 3.5±0.15    | 5.0±0.3    | 0.8±0.1  | 40                                          | 68     |
| HF70BB3.5X3X1.3    | 3.5±0.15    | 3.0±0.2    | 1.3±0.1  | 17                                          | 28     |
| HF70BB3.5X5X1.3    | 3.5±0.15    | 5.0±0.3    | 1.3±0.1  | 29                                          | 49     |
| HF70BB3.5X10X1.3   | 3.5±0.15    | 10.0±0.4   | 1.3±0.1  | 53                                          | 92     |
| HF70BB4.5X4X2.5    | 4.5±0.15    | 4.0±0.2    | 2.5±0.15 | 17                                          | 30     |
| HF70BB4.5X5X1.6    | 4.5±0.15    | 5.0±0.3    | 1.6±0.1  | 31                                          | 53     |
| HF70BB4X15X1.35    | 4+0.1, -0.2 | 15.0±0.5   | 1.35±0.1 | 92                                          | 155    |
| HF70BB5X5X2        | 5.0±0.15    | 5.0±0.3    | 2.0±0.15 | 27                                          | 42     |
| HF70BB5.5X5X2.5    | 5.5±0.2     | 5.0±0.3    | 2.5±0.15 | 22                                          | 38     |
| HF70BB6X3.8X3      | 6.0±0.2     | 3.8±0.2    | 3.0±0.2  | 19                                          | 31     |
| HF70BB6.4X4.5X3.2  | 6.4±0.2     | 4.5±0.2    | 3.2±0.15 | 22                                          | 37     |
| HF70BB6.4X5X3.2    | 6.4±0.2     | 5.0±0.2    | 3.2±0.15 | 20                                          | 32     |
| HF70BB6.4X10X3.2   | 6.4±0.2     | 10.0±0.5   | 3.2±0.15 | 40                                          | 63     |
| HF70BB9X5X4.5      | 9.0±0.25    | 5.0±0.3    | 4.5±0.15 | 20                                          | 34     |
| HF70BB9X10X4.5     | 9.0±0.25    | 10.0±0.4   | 4.5±0.15 | 40                                          | 68     |
| HF70BB9.5X10.4X4.9 | 9.52±0.25   | 10.42±0.25 | 4.9±0.15 | 40                                          | 70     |

## Ni-Zn BB series


## ELECTRICAL CHARACTERISTICS

## IMPEDANCE VS. FREQUENCY CHARACTERISTICS


HF30BB1.8X5X0.7




HF30BB2.5X2X0.8




HF30BB3X5X1




HF30BB3.5X5X1.3




HF30BB5X5X2




HF30BB6.4X5X3.2




HF40BB1.7X1.9X0.7




HF40BB3X5X1




HF40BB3.4X3X1




HF40BB3.5X5X1.3




HF40BB4.5X4X2.5-G




HF40BB4.5X5X1.6




HF40BB5X5X2



HF40BB5X6X2.5



HF40BB5.5X5X2.5




• All specifications are subject to change without notice.

## Ni-Zn BB series


## ELECTRICAL CHARACTERISTICS

## IMPEDANCE VS. FREQUENCY CHARACTERISTICS


## HF40BB6X3.8X3A-G




## HF57BB2.85X2X1.35




## HF57BB2.85X5X1.35




## HF57BB3.35X2X2




## HF57BB3.5X1X1.6




## HF57BB3.5X1.5X1.3




## HF57BB3.5X3X1.3




## HF57BB3.5X5X1.3




## HF57BB3.6X3.2X2.7




## HF57BB4X2X2




## HF57BB4X5X2



## HF57BB4.5X4X2.5



## HF57BB4.8X4.8X2.4




## Ni-Zn BB series


## ELECTRICAL CHARACTERISTICS

## IMPEDANCE VS. FREQUENCY CHARACTERISTICS


## HF57BB5X5X2




## HF70BB1.8X5X0.7




## HF70BB2.5X2.2X0.8




## HF70BB2.5X5X0.8




## HF70BB3X5X1




## HF70BB3.4X3X1




## HF70BB3.5X2X1.3




## HF70BB3.5X5X0.8




## HF70BB3.5X3X1.3




## HF70BB3.5X5X1.3




## HF70BB3.5X10X1.3



## HF70BB4.5X4X2.5



## HF70BB4.5X5X1.6




• All specifications are subject to change without notice.

## Ni-Zn BB series


## ■ ELECTRICAL CHARACTERISTICS

## □ IMPEDANCE VS. FREQUENCY CHARACTERISTICS


HF70BB4X15X1.35




HF70BB5X5X2




HF70BB5.5X5X2.5




HF70BB6X3.8X3




HF70BB6.4X4.5X3.2




HF70BB6.4X5X3.2




HF70BB6.4X10X3.2



HF70BB9X5X4.5



HF70BB9X10X4.5



HF70BB9.5X10.4X4.9

