

Housing - HC-D 25-SML-57/M1PG16 - 1772476

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Box mounting base, with single locking latch, height 57 mm, with screw connection, 1x Pg16



Key commercial data

Packing unit	1 PCE
Minimum order quantity	10 PCE
GTIN	 4 017918 037147
Custom tariff number	85389099
Country of origin	GERMANY

Technical data

General data

Note	For contact inserts HC-D25, A16
Design	D25
Height	57 mm
Width	50 mm
Length	109.5 mm
Housing type	Box mounting bases
Locking type	With single locking latch
No. of cable exits	1
Cable exit	Left (view of the opened single locking latch)
Screw connection	With
Type of the screw connection	1x Pg16
Wrench size, union nut	22 mm
External cable diameter	7.5 mm ... 15 mm

Housing - HC-D 25-SML-57/M1PG16 - 1772476

Technical data

General data

Degree of protection for housing	IP65
Ambient temperature (operation)	-40 °C ... 125 °C
Housing material	Aluminum die-cast
Housing surface material	Powder-coated, gray
Cable gland material	Nickel-plated brass
Cable seal material	NBR
Material lock	Steel, galvanized

Classifications

ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

UNSPSC

UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502
UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209

Approvals

Approvals

Approvals

GOST

Housing - HC-D 25-SML-57/M1PG16 - 1772476

Approvals

Ex Approvals

Approvals submitted

Approval details

GOST 

Drawings

Dimensioned drawing

