






LOC		DIST	P		ZONE	LTR	REVISIONS		DATE	APPD
AD	00						DESCRIPTION			
					AM		REV PER 063C-0515-04		07JAN05	JR/MM



THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

						PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± .010 ANGLES ± -		DR 8-11-93 A.STAUB B6		AMP AMP Incorporated Harrisburg, PA 17105-3608			
		CHK 3/23/94 H ROSE					
		MATERIAL		APPD 3/23/94 M THUMMA		NAME CONNECTOR ASSEMBLY, TWIN LEAF RIGHT ANGLE, CRIMP SNAP, .100 CENTERS	
SEE CALLOUT		PRODUCT SPEC -					
FINISH		APPLICATION SPEC -		SIZE D 00779 C-583900			
SEE CALLOUT		WEIGHT -					
						SHEET 1 OF 2	

CUSTOMER DRAWING

