





PCB Holes Diagram


Back View



Circuit Diagram

SPECIFICATION

1. Rating : DC 30V 0.5A;
2. Contact resistance: $\leq 50m\Omega$;
3. Insulation resistance: $\geq 100M\Omega$ (DC250V);
4. Withstand voltage: 500VAC ;
5. Insertion and extraction force: 3-30N;
6. life test: 5,000 cycles。



5	RING SPRING	3	1	1	QSn6.5-0.1 t=0.3	Sn-Plated
4	TIP SPRING	2	1	1	H62 t=0.3	Sn-Plated
3	EARTH SPRING	1	1	1	QSn6.5-0.1 t=0.35	Sn-Plated
2	BUSHING	1	1	1	BRASS	Ni-Plated
1	HOUSING	1	1	1	PA66	Black
NO.	PART NAME	TER.NO.	QTY	MATERIAL	REMARK	
TOLERANCE		UNITS	mm	NAME(INTENDED USE)		
0~6±0.1	X.*±1.5*	MAT'L		Top Willing		
6~20±0.2	.X*±1*			CUSTOMER		
20~90±0.3	.XX*±0.5*	FINISH		CUSTOMER		
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DHITAN PRECISION IND. CO., LTD. ANY REPRODUCTION OR COPIED FOR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DHITAN PRECISION IND. CO., LTD.		QTY		DR:	CH 2009/12/10	
PART NO.(INTENDED USE)		APPD:	DTJ-0400	DWG NO.: 2002-0400-001		
TITLE:		CHKD:		SCALE SHEET REV.		
CUSTOMER		DR:	CH 2009/12/10	N/A 1/1 A		