

Bügelmeßschraube

DIN 863
Ableseile mattverchromt
Spindel 6,5 mm Ø
HM-Messflächen
Ablesung 0,01 mm
Einstellmaß ab 25 mm
einschließlich Etui

Outside micrometers

DIN 863
satin chromed reading parts
spindle 6,5 mm Ø
reading 0,01 mm
carbide tipped measuring surfaces
individually packed

Micromètres

DIN 863
surfaces de lecture chromées mates
broche 6,5 mm Ø
lecture 0,01 mm
surface de mesure en carbure
avec étalon à partir de 25 mm
emballés en étui

> mm <	 mm	No.	€	Calibr. ...K	> mm <	 mm	No.	€
0-25	0,01	200-01	14,10	17,00	150-175	0,01	200-07	
25-50	0,01	200-02	16,90	29,00	175-200	0,01	200-08	
50-75	0,01	200-03	21,40	32,30	200-225	0,01	200-09	
75-100	0,01	200-04	25,95	32,30	225-250	0,01	200-10	
100-125	0,01	200-05	31,60	32,30	250-275	0,01	200-11	
125-150	0,01	200-06	36,10	32,30	275-300	0,01	200-12	


**Bügelmeßschraube
mit vorgezogener Gefühlsratsche**

DIN 863
Ableseile mattverchromt
HM-Messflächen
Ablesung 0,01 mm
Einstellmaß ab 25 mm
einschließlich Etui

**Outside micrometers
with friction clutch**

DIN 863
satin chromed reading parts
carbide tipped measuring surfaces
reading 0,01 mm
individually packed

**Micromètres
avec friction de contact**

DIN 863
surfaces de lecture chromées mates
surfaces de mesure en carbure
lecture 0,01 mm
avec étalon à partir de 25 mm
emballés en étui

> mm <	 mm	 mm	No.	€
0-25	0,01	6,5	200-15	
25-50	0,01	6,5	200-16	
50-75	0,01	6,5	200-17	
75-100	0,01	6,5	200-18	

**Bügelmeßschraube im Satz**

DIN 863
Ableseile mattverchromt
HM-Messflächen
Ablesung 0,01 mm
einschließlich Etui

Outside micrometer set

DIN 863
satin chromed reading parts
carbide tipped measuring surfaces
reading 0,01 mm
individually packed

Jeux de micromètres

DIN 863
surfaces de lecture chromées mates
surfaces de mesure en carbure
lecture 0,01 mm
emballés en étui

> mm <	 mm	 mm	No.	€
0-75	0,01	6,5	200-20	
0-100	0,01	6,5	200-21	
0-150	0,01	6,5	200-22	

200-22



> mm <



Messbereich
Ablesung mm / inch
Spindel

Range
Reading mm / inch
Spindle diam.

Capacité
Lecture mm / inch
Diam. broche