



## 1707




**1707-0-19-XX-30-XX-10-0**  
Press-fit in .061 mounting hole

## 0240




**0240-0-15-XX-30-XX-04-0**  
Press-fit in .059 mounting hole

## 0307




**0307-0-15-XX-30-XX-04-0**  
Press-fit in .059 mounting hole

## 1753



**1753-0-15-XX-30-XX-04-0**  
Press-fit in .057 mounting hole


## 1705/1706/1762



**17XX-0-15-XX-35-XX-04-0**  
Press-fit in .057 mounting hole

| Basic Part Number | Height A |
|-------------------|----------|
| 1705-0            | .165     |
| 1706-0            | .218     |
| 1762-0            | .300     |


## 0672



**0672-X-15-XX-30-XX-10-0**  
Swage mount in .049 hole

| Basic Part Number | Board Thickness | Length V |
|-------------------|-----------------|----------|
| 0672-1            | .031            | .052     |
| 0672-2            | .062            | .084     |
| 0672-3            | .094            | .115     |
| 0672-4            | .125            | .146     |


## 1024/1104



**1XX4-0-18-XX-30-XX-10-0**  
Press-fit in .059 mounting hole


| Basic Part Number | Length L |
|-------------------|----------|
| 1024-0            | .290     |
| 1104-0            | .450     |

## 0498



**0498-0-15-XX-35-XX-04-0**  
Press-fit in .057 mounting hole

## 8131



**8131-0-15-XX-30-XX-10-0**  
Press-fit in .057 mounting hole

### SPECIFICATIONS

**SHELL MATERIAL:**  
Brass Alloy 360, 1/2 Hard

**CONTACT MATERIAL:**  
Beryllium Copper Alloy 172, HT

**DIMENSION IN INCHES**  
**TOLERANCES ON:**  
LENGTHS: ±.005  
DIAMETERS: ±.002  
ANGLES: ± 2°

ORDER CODE: **XXXX - X - 1X - XX - XX - XX - XX - 0**

**BASIC PART #** →

**SPECIFY SHELL FINISH:**

**01** 200μ" TIN/LEAD OVER NICKEL

**80** 200μ" TIN OVER NICKEL

**15** 10μ" GOLD OVER NICKEL

**SPECIFY CONTACT FINISH:**

**02** 100μ" TIN/LEAD OVER NICKEL

**84** 100μ" TIN OVER NICKEL

**27** 30μ" GOLD OVER NICKEL



**SELECT CONTACT**

**#30 or #35 CONTACT (DATA ON PAGE 218 & 219)**