



**Advanced Power
Electronics Corp.**


AP6681GMT-HF

Halogen-Free Product

P-CHANNEL ENHANCEMENT MODE

POWER MOSFET

- ▼ Low On-resistance
- ▼ SO-8 Compatible
- ▼ Simple Drive Requirement
- ▼ RoHS Compliant & Halogen-Free




BV_{DSS}	-30V
$R_{DS(ON)}$	3.1m Ω
I_D	-135A

Description

Advanced Power MOSFETs from APEC provide the designer with the best combination of fast switching, ruggedized device design, low on-resistance and cost-effectiveness.

The PMPAK[®] 5x6 package is special for DC-DC converters application and the foot print is compatible with SO-8 with backside heat sink.



Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	-30	V
V_{GS}	Gate-Source Voltage	± 20	V
$I_D@T_C=25^\circ\text{C}$	Continuous Drain Current (Chip), V_{GS} @ 10V	-135	A
$I_D@T_A=25^\circ\text{C}$	Continuous Drain Current ³ , V_{GS} @ 10V	-33	A
$I_D@T_A=70^\circ\text{C}$	Continuous Drain Current ³ , V_{GS} @ 10V	-26.4	A
I_{DM}	Pulsed Drain Current ¹	-200	A
$P_D@T_C=25^\circ\text{C}$	Total Power Dissipation	83.3	W
$P_D@T_A=25^\circ\text{C}$	Total Power Dissipation	5	W
T_{STG}	Storage Temperature Range	-55 to 150	$^\circ\text{C}$
T_J	Operating Junction Temperature Range	-55 to 150	$^\circ\text{C}$

Thermal Data

Symbol	Parameter	Value	Unit
Rthj-c	Maximum Thermal Resistance, Junction-case	1.5	$^\circ\text{C}/\text{W}$
Rthj-a	Maximum Thermal Resistance, Junction-ambient ³	25	$^\circ\text{C}/\text{W}$



AP6681GMT-HF

Electrical Characteristics@T_j=25°C(unless otherwise specified)

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Units
BV _{DSS}	Drain-Source Breakdown Voltage	V _{GS} =0V, I _D =-250uA	-30	-	-	V
R _{DS(ON)}	Static Drain-Source On-Resistance ²	V _{GS} =-10V, I _D =-20A	-	2.7	3.1	mΩ
		V _{GS} =-4.5V, I _D =-20A	-	3.9	4.6	mΩ
V _{GS(th)}	Gate Threshold Voltage	V _{DS} =V _{GS} , I _D =-250uA	-1	-1.45	-3	V
g _{fs}	Forward Transconductance	V _{DS} =-10V, I _D =-20A	-	66	-	S
I _{DSS}	Drain-Source Leakage Current	V _{DS} =-24V, V _{GS} =0V	-	-	-10	uA
I _{GSS}	Gate-Source Leakage	V _{GS} =±20V, V _{DS} =0V	-	-	±100	nA
Q _g	Total Gate Charge	I _D =-20A	-	94	150	nC
Q _{gs}	Gate-Source Charge	V _{DS} =-15V	-	25	-	nC
Q _{gd}	Gate-Drain ("Miller") Charge	V _{GS} =-4.5V	-	38	-	nC
t _{d(on)}	Turn-on Delay Time	V _{DS} =-15V	-	20	-	ns
t _r	Rise Time	I _D =-1A	-	14	-	ns
t _{d(off)}	Turn-off Delay Time	R _G =3.3Ω	-	210	-	ns
t _f	Fall Time	V _{GS} =-10V	-	84	-	ns
C _{iss}	Input Capacitance	V _{GS} =0V	-	13800	22080	pF
C _{oss}	Output Capacitance	V _{DS} =-15V	-	1060	-	pF
C _{rss}	Reverse Transfer Capacitance	f=1.0MHz	-	800	-	pF
R _g	Gate Resistance	f=1.0MHz	-	2.7	5.4	Ω

Source-Drain Diode

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Units
V _{SD}	Forward On Voltage ²	I _S =-20A, V _{GS} =0V	-	-	-1.2	V
t _{rr}	Reverse Recovery Time	I _S =-10A, V _{GS} =0V,	-	45	-	ns
Q _{rr}	Reverse Recovery Charge	dI/dt=100A/μs	-	50	-	nC

Notes:







- 1.Pulse width limited by Max. junction temperature.
- 2.Pulse test
- 3.Surface mounted on 1 in² copper pad of FR4 board, t ≤10sec ; 60°C/W at steady state.

THIS PRODUCT IS SENSITIVE TO ELECTROSTATIC DISCHARGE, PLEASE HANDLE WITH CAUTION.

USE OF THIS PRODUCT AS A CRITICAL COMPONENT IN LIFE SUPPORT OR OTHER SIMILAR SYSTEMS IS NOT AUTHORIZED.

APEC DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

APEC RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN.





AP6681GMT-HF




Fig 7. Gate Charge Characteristics




Fig 8. Typical Capacitance Characteristics




Fig 9. Maximum Safe Operating Area




Fig 10. Effective Transient Thermal Impedance




Fig 11. Transfer Characteristics




Fig 12. Maximum Continuous Drain Current v.s. Case Temperature