

[Skip to content](#)

Search By: Part Number Text [Tips](#)



Sunday, September 10, 2006

[Sign In](#)

[Home](#) > [Products](#) > [By Type](#) > [PolySwitch Resettable Devices](#) > [Product Feature Selector](#) > Product Details

Product Details for RXEF017-2



RXEF017-2

Tyco Part Number: E20890-000



[Active](#)

PolySwitch Resettable Devices



[RoHS Compliant](#)

Product Highlights:

- Radial Application
- Family Name = RXEF
- Through Hole Construction
- Radial Construction
- IH (Room Temperature) = .17 Amps.

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [RXEF017](#) (PDF, English)

Catalog Pages/ Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features: - UL Recognized = File No. E74889 Electrical Characteristics: IH (Room Temperature) (Amps.) = 0.17 IT (Room Temperature) (Amps.) = 0.34 Vmax Operating (V) = 60 Rmin (Ω) = 3.30 Rmax (Ω) = 5.210 R1 Max [Post Trip] (Ω) = 8.00 UL Rated Current (Amps.) = 40 - Tripped Power Dissipation (Typical) (W) = 0.48 Termination Related Features: - Construction = Radial, Through Hole Body Related Features: - Lead Type = Standard Kinked Lead - CSA File No. = 78165C Contact Related Features: - Family Name = RXEF	Configuration Related Features: - Coating = Coated Industry Standards: RoHS/ELV Compliance = RoHS compliant, ELV compliant Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C - RoHS/ELV Compliance History = Always was RoHS compliant - TUV Certificate No. = R72041428 Conditions for Usage: Operating Temperature (Max.) (°C) = 85 Operation / Application: - Application = Radial Packaging Related Features: - Packaging Method = Tape & Reel Other: - Brand = Raychem
---	---

Languages: English | [Deutsch](#) | [Español](#) | [Português \(do Brasil\)](#) | [Русский](#) | [Italiano](#) | [正體中文 \(繁體\)](#) | [中文 \(简体\)](#) | [日本語](#)
Country Sites: [China](#) | [Japan](#)