

A



Geom. Spec: N/A

$$B \quad - \quad \text{---} \quad - \quad A$$

Geom. Spec: N/A

- 1 Product and Processing must meet requirements of Tyco Electronics Standard 230-702
- 2 Includes dust caps (not shown on print).
- 3 IL tested at 1300nm.
- 4 Label 2 will not be present on any cable assembly less than 5 meters long.

DIMENSIONS: meters		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK Dave Fennell		Tyco Electronics, Inc. Harrisburg, PA 17105-3608	
		0 P/LC ± . 1 P/LC ± . 2 P/LC ± . 3 P/LC ± . 4 P/LC ± .		APVD Dave Fennell			
				NAME FO C/A - 2 fiber, 50/125, OFNP (Plenum) jacket, LC-Duplex Secure to SC-Duplex			
Restricted To:		NTS SIZE A2		DRAWING NO C- 1905002		SHEET 1 of 4	
						REV A	

THIS DRAWING IS A CONTROLLED DOCUMENT.

CAC Customer Layout Rev: D

LOC
CE
DIST
16

8	7	6	5	4	3	2	1
---	---	---	---	---	---	---	---

		DIMENSIONS: meters		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK Dave Fennell			
				Ø P L C 1 P L C 2 P L C 3 P L C 4 P L C	+ - + + +	APVD Dave Fennell		 Tyco Electronics, Inc. Harrisburg, PA 17105-3608	
07	-	DF	Restricted To:			NAME FO C/A - 2 fiber, 50/125, OFNP (Plenum) jacket, LC-Duplex Secure to SC-Duplex			
ITE	DN	APVD				SCALE NTS		SHEET 2 of 4	
			SIZE A2		DRAWING NO C- 1905002				

USED ON	
---------	--

ON GND

THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

Part #	L (meters)	L (feet)	LC-Duplex Secure, Red		SC-Duplex, Beige	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
4-1905002-3	42.570 - 43.430	139.66 - 142.48	0.56	-	0.56	-
4-1905002-4	43.560 - 44.440	142.91 - 145.80	0.57	-	0.57	-
4-1905002-5	44.550 - 45.450	146.16 - 149.11	0.57	-	0.57	-
4-1905002-6	45.540 - 46.460	149.40 - 152.42	0.57	-	0.57	-
4-1905002-7	46.530 - 47.470	152.65 - 155.74	0.57	-	0.57	-
4-1905002-8	47.520 - 48.480	155.90 - 159.05	0.57	-	0.57	-
4-1905002-9	48.510 - 49.490	159.15 - 162.36	0.57	-	0.57	-
5-1905002-0	49.500 - 50.500	162.40 - 165.68	0.58	-	0.58	-
5-1905002-1	50.490 - 51.510	165.64 - 168.99	0.58	-	0.58	-
5-1905002-2	51.480 - 52.520	168.89 - 172.30	0.58	-	0.58	-
5-1905002-3	52.470 - 53.530	172.14 - 175.62	0.58	-	0.58	-
5-1905002-4	53.460 - 54.540	175.39 - 178.93	0.58	-	0.58	-
5-1905002-5	54.450 - 55.550	178.64 - 182.25	0.58	-	0.58	-
5-1905002-6	55.440 - 56.560	181.88 - 185.56	0.58	-	0.58	-
5-1905002-7	56.430 - 57.570	185.13 - 188.87	0.59	-	0.59	-
5-1905002-8	57.420 - 58.580	188.38 - 192.19	0.59	-	0.59	-
5-1905002-9	58.410 - 59.590	191.63 - 195.50	0.59	-	0.59	-
6-1905002-0	59.400 - 60.600	194.88 - 198.81	0.59	-	0.59	-
6-1905002-1	60.390 - 61.610	198.12 - 202.13	0.59	-	0.59	-
6-1905002-2	61.380 - 62.620	201.37 - 205.44	0.59	-	0.59	-
6-1905002-3	62.370 - 63.630	204.62 - 208.75	0.59	-	0.59	-
6-1905002-4	63.360 - 64.640	207.87 - 212.07	0.6	-	0.6	-
6-1905002-5	64.350 - 65.650	211.12 - 215.38	0.6	-	0.6	-
6-1905002-6	65.340 - 66.660	214.37 - 218.70	0.6	-	0.6	-
6-1905002-7	66.330 - 67.670	217.61 - 222.01	0.6	-	0.6	-
6-1905002-8	67.320 - 68.680	220.86 - 225.32	0.6	-	0.6	-
6-1905002-9	68.310 - 69.690	224.11 - 228.64	0.6	-	0.6	-
7-1905002-0	69.300 - 70.700	227.36 - 231.95	0.61	-	0.61	-
7-1905002-1	70.290 - 71.710	230.61 - 235.26	0.61	-	0.61	-
7-1905002-2	71.280 - 72.720	233.85 - 238.58	0.61	-	0.61	-
7-1905002-3	72.270 - 73.730	237.10 - 241.89	0.61	-	0.61	-
7-1905002-4	73.260 - 74.740	240.35 - 245.20	0.61	-	0.61	-
7-1905002-5	74.250 - 75.750	243.60 - 248.52	0.61	-	0.61	-
7-1905002-6	75.240 - 76.760	246.85 - 251.83	0.61	-	0.61	-
7-1905002-7	76.230 - 77.770	250.09 - 255.15	0.62	-	0.62	-
7-1905002-8	77.220 - 78.780	253.34 - 258.46	0.62	-	0.62	-
7-1905002-9	78.210 - 79.790	256.59 - 261.77	0.62	-	0.62	-
8-1905002-0	79.200 - 80.800	259.84 - 265.09	0.62	-	0.62	-

	A	Rev Per EC# None	7/30/2007	-	D
P	LTR	REVISION RECORD	DATE	DIN	AP

DIMENSIONS;
meters



TOLERANCES UNLESS OTHERWISE SPECIFIED		
0 PLC	±	-
1 PLC	±	-
2 PLC	±	-
3 PLC	±	-
4 PLC	±	-

Restricted To:

Cable Assy Configurator		MATERIAL		HEAT TREAT	
OK Dave Fennell		-		-	
APVD Dave Fennell		 Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
NAME FO C/A - 2 fiber, 50/125, OFNP (Plenum) jacket, LC-Duplex Secure to SC-Duplex					
SCALE NTS	SIZE A2	DRAWING NO. C- 1905002	SHEET 3 of 4	REV A	

D

C

3

A

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

THIS DRAWING IS A CONTROLLED DOCUMENT.
REV NO

LOC
CE
DIST
16

CAC Customer Layout Rev: D

8

7

6

5

4

3

2

1

Label 1

Per specification 107-1645-1



Trace # - Bar Code

Trace # - Human Readable


Part Number

Country of Origin

This label is used on all lengths on this drawing.

Label 2

Per specification 107-1645-1



Trace # - Bar Code

Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.

	A	Rev Per EC#	None	7/30/2007	-	DF			
P	LTR	REVISION RECORD		DATE	DIN	APVD			

DIMENSIONS:
meters

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 P.L.C. ± .
1 P.L.C. ± .
2 P.L.C. ± .
3 P.L.C. ± .
4 P.L.C. ± .

Restricted To:

DIN		Cable Assy Configurator		MATERIAL		HEAT TREAT			
CHK		Dave Fennell		AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608					
APVD		Dave Fennell							
NAME								FO C/A - 2 fiber, 50/125, OFNP (Plenum) jacket, LC-Duplex Secure to SC-Duplex	
SCALE		SIZE		DRAWING NO		SHEET		REV	
NTS		A2		C- 1905002		4 of 4		A	