




- | |
|-----------------------------|
| SUPERSEDED BY
5-641127-8 |
| SUPERSEDED BY
5-641127-7 |
| SUPERSEDED BY
5-641127-6 |
| SUPERSEDED BY
5-641127-5 |
| SUPERSEDED BY
5-641127-4 |
| SUPERSEDED BY
5-641127-3 |
| SUPERSEDED BY
5-641127-2 |
| SUPERSEDED BY
5-641127-1 |
| SUPERSEDED BY
5-641127-0 |
| SUPERSEDED BY
4-641127-9 |
| SUPERSEDED BY
4-641127-8 |
| SUPERSEDED BY
4-641127-7 |

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN 26-JAN-2005 S. HOOVER QIR D. BOSSI 26-JAN-2005 APPROVED D. BOSSI 26-JAN-2005 PRODUCT SPEC		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 0.13 [0.005] 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH		NAME MTA-100 HEADER ASSEMBLY, FRICTION LOCK, NOTCHED, .025 SQUARE RIGHT ANGLE POST, .000015 GOLD PLATED	
MATERIAL 		APPLICATION SPEC WEIGHT		SIZE CAGE CODE DRAWING NO A1 00779 C=641127	
		CUSTOMER DRAWING		SCALE: 8:1 SHEET 1 of 1 REV. AC1	