



The PCI-9114 also features 1-CH 16-bit general-purpose timer/counter, 16-CH TTL isolated digital inputs and 16-CH TTL isolated digital outputs. ADLINK PCI-9114 delivers cost-effective and reliable data acquisition capabilities and is ideal for a broad variety of applications.

- Supports a 32-bit 5 V PCI bus
- 16-bit A/D resolution
- Up to 100 kS/s sampling rate (PCI-9114DG)
- Up to 250 kS/s sampling rate (PCI-9114A-DG and PCI-9114A-HG)
- 32-CH single-ended or 16-CH differential analog inputs
- Bipolar or unipolar analog input ranges
- Onboard 1 k-sample A/D FIFO
- Programmable gains:
 - x1, x2, x4, x8 (PCI-9114DG and PCI-9114A-DG)
 - x1, x10, x100 (PCI-9114A-HG)
- Automatic analog inputs scanning
- 16-CH isolated digital inputs and 16-CH isolated digital outputs
- 2500 V_{RMS} optical isolation for digital inputs and outputs
- 1-CH 16-bit general-purpose timer/counter
- +12 V and -12 V power available on the 37-pin D-sub connector
- Onboard resettable fuses for power output protection
- Compact, half-size PCB
- **Operating Systems**
 - Windows 7/Vista/XP/2000/2003 Server
 - Linux
- **Recommended Software**
 - AD-Logger
 - VB.NET/VC.NET/VB/VB++ + BCB/Delphi
 - DAQBench
- **Drivers Support**
 - DAQPilot for LabVIEW™
 - DAQ-MTLB for MATLABR
 - PCIS-DASK for Windows
 - PCIS-DASK/X for Linux

Analog Input

- Number of channels: 32 single-ended or 16 differential
- Resolution: 16 bits
- Conversion time:
 - 10 μ s (PCI-9114DG)
 - 4 μ s (PCI-9114A-DG & PCI-9114A-HG)
- Maximum sampling rate

- Input ranges (software programmable)

Device	Gain	Input Range
PCI-9114DG PCI-9114A-DG	1	$\pm 10\text{ V}$
	2	$\pm 5\text{ V}$
	4	$\pm 2.5\text{ V}$
	8	$\pm 1.25\text{ V}$
PCI-9114A-HG	1	$\pm 10\text{ V}$
	10	$\pm 1\text{ V}$
	100	$\pm 0.1\text{ V}$

- Accuracy

Device	Gain	Input Range
PCI-9114DG	1	0.01% of FSR \pm 1 LSB
PCI-9114A-DG	2,4	0.02% of FSR \pm 1 LSB
	8	0.04% of FSR \pm 1 LSB
PCI-9114A-HG	1, 10	0.01% of FSR \pm 1 LSB
	100	0.02% of FSR \pm 1 LSB

- Input coupling: DC
- Overvoltage protection: continuous $\pm 35\text{ V}$
- Input impedance: $1\text{ G}\Omega$
- Trigger modes: software, pacer, and external trigger (5 V/TTL compatible)
- FIFO buffer size: 1 k samples
- Data transfers: polling, interrupt

Isolated Digital Input

- Number of channels: 16
- Maximum input range: 24 V, non-polarity
- Digital logic levels
 - 0 - 24 V, non-polarity
 - Input high voltage: 5 - 24 V
 - Input low voltage: 0 - 1.5 V
- Input resistance: 2.4 K Ω @ 0.5 W
- Isolation voltage: 2500 VRMS
- Data transfers: programmed I/O

Isolated Digital Output

- Number of channels: 16
- Output type: open emitter Darlington transistors
- Sink current
 - 350 mA for one channel @ 100% duty
 - 260 mA for all channels @ 10% duty
- Power dissipation: Max. 1.47 W per chip (8 DO channels)
- Supply voltage: 5-35 V
- Isolation voltage: 2500 VRMS
- Data transfers: programmed I/O

Power Output

- Output voltage: +12 V and -12 V
- Resettable fuse protection: 500 mA

General-Purpose Timer/Counter

- Number of channels: 1
- Resolution: 16 bits
- Compatibility: 5 V/TTL
- Base clock available: 2 MHz, external clock to 2 MHz

General Specifications

- I/O connector
 - 37-pin D-sub female
 - 20-pin ribbon male x 2
- Operating temperature: 0°C to 55°C
- Storage temperature: -20°C to 80°C
- Relative humidity: 5% to 95%, non-condensing
- Power requirements

+5 V	+12 V
600 mA typical	100 mA typical
- Dimensions (not including connectors)
175 mm x 107 mm

■ DIN-37D-01*

Terminal Board with One 37-pin D-sub Connector and DIN-Rail Mounting

■ DIN-20P-01*

Terminal Board with One 20-pin Ribbon Connector and DIN-Rail Mounting

■ ACLD-9137-01

General-Purpose Terminal Board with One 37-pin D-sub Male Connector

■ ACLD-9188-01*

General-Purpose Terminal Board with Two 20-pin Ribbon Connectors and One 37-pin D-sub Connector

* Cables are not included. For information on mating cables, refer to P2-61/62

■ PCI-9114DG

32-CH 16-Bit 100 kS/s Normal-Gain Multi-Function DAQ Card

■ PCI-9114A-DG

32-CH 16-Bit 250 kS/s Normal-Gain Multi-Function DAO Card

■ PCI-9114A-HG

32-CH 16-Bit 250 kS/s High-Gain Multi-Function DAQ Card

Pin Assignment

CN1				CN2			
+12Vout	1	20	GND	DI_0	1	2	DI_8
-12Vout	2	21	(AIL15) AI31	DI_1	3	4	DI_9
AI15 (AIH15)	3	22	(AIL14) AI30	DI_2	5	6	DI_10
AI14 (AIH14)	4	23	(AI13) AI29	DI_3	7	8	DI_11
AI13 (AIH13)	5	24	(AIL12) AI28	DI_4	9	10	DI_12
AI12 (AIH12)	6	25	(AIL11) AI27	DI_5	11	12	DI_13
AI11 (AIH11)	7	26	(AIL10) AI26	DI_6	13	14	DI_14
AI10 (AIH10)	8	27	(AIL9) AI25	DI_7	15	16	DI_15
AI9 (AIH9)	9	28	(AIL8) AI24	EICOM1	17	18	EICOM3
AI8 (AIH8)	10	29	AGND	EICOM2	19	20	EICOM4
AGND	11	30	(AIL7) AI23	CN3			
AI7 (AIH7)	12	31	(AIL6) AI22	DO_0	1	2	DO_8
AI6 (AIH6)	13	32	(AIL5) AI21	DO_1	3	4	DO_9
AI5 (AIH5)	14	33	(AIL4) AI20	DO_2	5	6	DO_10
AI4 (AIH4)	15	34	(AIL3) AI19	DO_3	7	8	DO_11
AI3 (AIH3)	16	35	(AIL2) AI18	DO_4	9	10	DO_12
AI2 (AIH2)	17	36	(AIL1) AI17	DO_5	11	12	DO_13
AI1 (AIH1)	18	37	(AIL0) AI16	DO_6	13	14	DO_14
AI0 (AIH0)	19			DO_7	15	16	DO_15
				EOGND	17	18	EOGND
				VDD	19	20	VDD

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ADLINK Technology:](#)

[PCI-9114DG](#) [PCI-9114A-DG](#) [PCI-9114A-HG](#) [PCI-9114HG](#)