

AVO75 Series

75 Watts

Data Sheet


Total Power: 75 Watts
Input Voltage: 36 - 75 V
of Outputs: Single

SPECIAL FEATURES

- 2:1 Wide input range
- Optimised for high density, small space applications
- Low ripple and noise
- Fixed switching frequency
- High efficiency
- High capacitive load capability
- Basic insulation system
- Pre-bias start-up capability
- Open-frame structure

SAFETY

- UL, cUL: UL60950
- TUV/CE: IEC/EN60950



Electrical Specifications

Input	
Input range:	36 - 75 VDC
Efficiency ² :	91% @ 12V
Output	
Voltage tolerance:	+/-1.2% to +/-1.6%
Line regulation:	5V: 4mV; 12V: 9mV; Others: 1mV
Load regulation:	5V and 12V: 5mV; Others: 1mV
Noise/ripple:	3.3 Vo: 1.2V, 2.5V, 3.3V: 50mV; 5V, 5.0 Vo: 12V: 55mV; 1.8V: 45mV
Over voltage protection:	Auto-restart
Over temperature protection:	
Switching frequency:	310 KHz
Temperature coefficient:	±0.02/°C
Isolation	
I/O isolation:	2000 VDC min.

Environmental Specifications

Operating ambient temperature range:	-40 °C to +85 °C
Storage temperature:	-55 °C to +125 °C
Humidity:	5% to 95% (non-condensing)
MTBF:	2.5 Million hours
RoHS Compliant	


Ordering Information

Model number	Input voltage	Output voltage	Power
AVO75-48S1V2-4	36 - 75 Vin	1.2V @ 25A	30W
AVO75-48S1V2P-4	36 - 75 Vin	1.2V @ 25A	30W
AVO75-48S1V8-4	36 - 75 Vin	1.8V @ 25A	45W
AVO75-48S1V8P-4	36 - 75 Vin	1.8V @ 25A	45W
AVO75-48S2V5-4	36 - 75 Vin	2.5V @ 25A	62.5W
AVO75-48S2V5P-4	36 - 75 Vin	2.5V @ 25A	62.5W
AVO75-48S3V3-4	36 - 75 Vin	3.3V @ 20A	66W
AVO75-48S05-4	36 - 75 Vin	5V @ 15A	75W
AVO75-48S05-6	36 - 75 Vin	5V @ 15A	75W
AVO75-48S05P-4	36 - 75 Vin	5V @ 15A	75W
AVO75-48S12P-4	36 - 75 Vin	12V @ 6.3A	75W

- Standard version is negative enable
- "-6" = 3.8mm pin length
- "-4" = 4.8mm pin length
- "-P" = Positive enable

Mechanical Drawings

Top & pin side view



Pin Length Option

Device Code Suffix	L
-4	4.8mm+/-0.5mm
-6	3.8mm+/-0.5mm
-8	2.8mm+/-0.25mm
NONE	5.8mm+/-0.5mm

Notes:

1. Un-dimensioned components are for visual reference only.
2. Pins 1~3, 5~7 are 1.0mm diameter with 2.0mm diameter standoff shoulders.
3. Pins 4, 8 are 1.5mm diameter with no standoff shoulders.

Pin Designations

Pin No.	Function	Pin No.	Function
1	+Vin	5	+Sense
2	CNT	6	Trim
3	-Vin	7	-Sense
4	+Vo	8	-Vo

Notes:

1. All specifications are subject to change without notice. Mechanical drawings are for reference only.
2. Warranty: 2 years
3. Label and logo appearance may vary from what is shown on mechanical drawings.

WORLDWIDE OFFICES

Americas

2900 S.Diablo Way
Tempe, AZ 85282
USA
+1 888 412 7832

Europe (UK)

Waterfront Business Park
Merry Hill, Dudley
West Midlands, DY5 1LX
United Kingdom
+44 (0) 1384 842 211

Asia (HK)

14/F, Lu Plaza
2 Wing Yip Street
Kwun Tong, Kowloon
Hong Kong
+852 2176 3333

ARTESYN[™]
EMBEDDED TECHNOLOGIES

www.artesyn.com

While every precaution has been taken to ensure accuracy and completeness in this literature, Artesyn Embedded Technologies assumes no responsibility, and disclaims all liability for damages resulting from use of this information or for any errors or omissions. Artesyn Embedded Technologies, Artesyn and the Artesyn Embedded Technologies logo are trademarks and service marks of Artesyn Embedded Technologies, Inc. All other names and logos referred to are trade names, trademarks, or registered trademarks of their respective owners. © 2014 Artesyn Embedded Technologies, Inc.

For more information: www.artesyn.com/power
For support: productsupport.ep@artesyn.com