


## ENERGIZER EN91

AA



### Industry Standard Dimensions




### Specifications

**NOT INTENDED FOR RETAIL TRADE**

|                         |                                        |
|-------------------------|----------------------------------------|
| <b>Classification:</b>  | Alkaline                               |
| <b>Chemical System:</b> | Zinc-Manganese Dioxide ( $Zn/MnO_2$ )  |
|                         | No added mercury or cadmium            |
| <b>Designation:</b>     | ANSI-15A, IEC-LR6                      |
| <b>Nominal Voltage:</b> | 1.5 volts                              |
| <b>Nominal IR:</b>      | 150 to 300 milliohms (fresh)           |
| <b>Operating Temp:</b>  | -18°C to 55°C (0°F to 130°F)           |
| <b>Typical Weight:</b>  | 23.0 grams (0.8 oz.)                   |
| <b>Typical Volume:</b>  | 8.1 cubic centimeters (0.5 cubic inch) |
| <b>Jacket:</b>          | Plastic Label                          |
| <b>Shelf Life:</b>      | 7 years at 21°C                        |
| <b>Terminal:</b>        | Flat Contact                           |


### Milliamp-Hours Capacity

Continuous discharge to 0.8 volts at 21°C




### Constant Power Performance

Typical Characteristics (21°C)



### Constant Current Performance

Typical Characteristics (21°C)



### Important Notice


This data sheet contains typical information specific to products manufactured at the time of its publication.  
©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.

# ENERGIZER EN91

AA


## Constant Power Performance

Discharge Characteristics (21°C)







## Constant Current Performance

250 mA Discharge (-20°C / 0°C / 21°C)



## Industry Standard Tests (21°C)



## Important Notice

This data sheet contains typical information specific to products manufactured at the time of its publication.  
©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.