


**KEMET Part Number: T491C226K016ZG** **Obsolete**  
(B45198H3226K309)



B45198H, Tantalum, MnO2 Tantalum, 22 uF, 10%, 16 V, SMD, Molded, 6032, Height Max = 2.8mm



#### General Information

Supplier:	KEMET
Series:	B45198H
Dielectric:	MnO2 Tantalum
Style:	SMD Chip
Description:	SMD, Molded
RoHS:	Yes
Termination:	Gold
Notes:	Old Part Number [Obsolete] Was B45198H3226K309

#### Dimensions

Footprint	6032
L	6mm +/-0.3mm
W	3.2mm +/-0.3mm
H	2.5mm +/-0.3mm
S	1.3mm +/-0.3mm
F	2.2mm +/-0.1mm
K	1.8mm TYP

#### Specifications

Capacitance:	22 uF
Capacitance Tolerance:	10%
Voltage DC:	16 VDC (85C), 10.72 VDC (125C)
Temperature Range:	-55/+125C
Rated Temperature:	85C
Dissipation Factor:	6%
Failure Rate:	N/A
Leakage Current:	3.5 uA

#### Packaging Specifications

Packaging:	T&R, 178mm
Packaging Quantity:	750