





P	LTR	DESCRIPTION	DATE	DWN	APVD
	AD	REVISED PER ECR-12-013445	18OCT12	KH	PD


- 1 CONTINUOUS STRIP ON REELS
- 2 MAX FIRST INSERTION FORCE, 88.96 NEWTON [20 LBS] USING GAGE 100505.
- 3 WIRE SIZE IS #14-10 AWG
- 4 INSULATION RANGE IS 3.81-5.08 [.150-.200] DIA
- 5 MATING TAB THK IS 0.81±0.025 [.032±.001]
- 6 FOREIGN PRODUCTION ONLY
- 7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



VIEW A-A
SCALE 10:1



SECTION B-B
SCALE 8:1



SECTION C-C
SCALE 8:1

F	5.33 [.210]	6.4 [.252]	F	3.30 [.130]	2.108 [083] 2.413 [095] 2.921 [115]	2.0mm [14] 3.0mm [12] 5.0mm [10]
TYPE	WIDTH	STRIP LENGTH ±0.38 ±[.015]	TYPE	WIDTH	±.051 [±.002] HEIGHT	WIRE
INSUL BARREL CRIMP	WIRE BARREL CRIMP					

6/Δ	OBSOLETE	SILVER	TEMP3 PHOS BRZ	Δ	42437-6
		TIN	TEMP3 PHOS BRZ	Δ	42437-5
	OBSOLETE	-	TEMP3 PHOS BRZ	Δ	42437-4
	OBSOLETE	SILVER	TEMP4 BRASS		42437-3
		TIN	BRASS		42437-2
	OBSOLETE	-	TEMP4 BRASS		42437-1
		FINISH	MATERIAL		PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN JR RUTH	7/10/89	 TE Connectivity					
DIMENSIONS: mm [INCHES]			CHK MS FEHER	7/10/89						
			TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C MEYERS	7/10/89	NAME RECEPTACLE, FASTON, 			