

HALF-BRIDGE DRIVER

Features

- Floating channel designed for bootstrap operation
- Fully operational to +600 V
- Tolerant to negative transient voltage, dV/dt immune
- Gate drive supply range from 10 V to 20 V
- Undervoltage lockout
- 3.3 V, 5 V, and 15 V logic compatible
- Cross-conduction prevention logic
- Matched propagation delay for both channels
- Internal set deadtime
- High side output in phase with H_{IN} input
- Low side output out of phase with $\overline{LIN}$ input

Product Summary

V _{OFFSET}	600 V max.
I _{O+/-}	130 mA/270 mA
V _{OUT}	10 V - 20 V
t _{on/off} (typ.)	680 ns/150 ns
Deadtime (typ.)	520 ns

Description


The IRS2103 is a high voltage, high speed power MOSFET and IGBT drivers with dependent high and low side referenced output channels. Proprietary HVIC and latch immune CMOS technologies enable ruggedized monolithic construction. The logic input is compatible with standard CMOS or LSTTL output, down to 3.3 V logic. The output drivers feature a high pulse current buffer stage designed for minimum driver cross-conduction. The floating channel can be used to drive an N-channel power MOSFET or IGBT in the high side configuration which operates up to 600 V.

Packages

8-Lead PDIP
IRS2103

8-Lead SOIC
IRS2103S

Typical Connection



(Refer to Lead Assignments for correct configuration). This diagram shows electrical connections only. Please refer to our Application Notes and Design Tips for proper circuit board layout.

Absolute Maximum Ratings

Absolute maximum ratings indicate sustained limits beyond which damage to the device may occur. All voltage parameters are absolute voltages referenced to COM. The thermal resistance and power dissipation ratings are measured under board mounted and still air conditions.

Symbol	Definition		Min.	Max.	Units
V _B	High side floating absolute voltage		-0.3	625	V
V _S	High side floating supply offset voltage		V _B - 25	V _B + 0.3	
V _{HO}	High side floating output voltage		V _S - 0.3	V _B + 0.3	
V _{CC}	Low side and logic fixed supply voltage		-0.3	25	
V _{LO}	Low side output voltage		-0.3	V _{CC} + 0.3	
V _{IN}	Logic input voltage (H _{IN} & $\overline{\text{LIN}}$)		-0.3	V _{CC} + 0.3	
dV _S /dt	Allowable offset supply voltage transient		—	50	V/ns
P _D	Package power dissipation @ T _A ≤ +25 °C	(8 Lead PDIP)	—	1.0	W
		(8 Lead SOIC)	—	0.625	
R _{thJA}	Thermal resistance, junction to ambient	(8 Lead PDIP)	—	125	°C/W
		(8 Lead SOIC)	—	200	
T _J	Junction temperature		—	150	°C
T _S	Storage temperature		-55	150	
T _L	Lead temperature (soldering, 10 seconds)		—	300	

Recommended Operating Conditions

The input/output logic timing diagram is shown in Fig. 1. For proper operation the device should be used within the recommended conditions. The V_S offset rating is tested with all supplies biased at a 15 V differential.

Symbol	Definition	Min.	Max.	Units
V_B	High side floating supply absolute voltage	$V_S + 10$	$V_S + 20$	V
V_S	High side floating supply offset voltage	Note 1	600	
V_{HO}	High side floating output voltage	V_S	V_B	
V_{CC}	Low side and logic fixed supply voltage	10	20	
V_{LO}	Low side output voltage	0	V_{CC}	
V_{IN}	Logic input voltage (HIN & $\overline{LIN}$)	0	V_{CC}	
T_A	Ambient temperature	-40	125	$^\circ\text{C}$

Note 1: Logic operational for V_S of -5 V to +600 V. Logic state held for V_S of -5 V to $-V_{BS}$. (Please refer to the Design Tip DT97-3 for more details).

Dynamic Electrical Characteristics

V_{BIAS} (V_{CC} , V_{BS}) = 15 V, C_L = 1000 pF and T_A = 25 °C unless otherwise specified.


Symbol	Definition	Min.	Typ.	Max.	Units	Test Conditions
t_{on}	Turn-on propagation delay	—	680	820	ns	$V_S = 0$ V
t_{off}	Turn-off propagation delay	—	150	220		$V_S = 600$ V
t_r	Turn-on rise time	—	70	170		
t_f	Turn-off fall time	—	35	90		
DT	Deadtime, LS turn-off to HS turn-on & HS turn-on to LS turn-off	400	520	650		
MT	Delay matching, HS & LS turn-on/off	—	—	60		

Static Electrical Characteristics

V_{BIAS} (V_{CC} , V_{BS}) = 15 V and T_A = 25 °C unless otherwise specified. The V_{IN} , V_{TH} , and I_{IN} parameters are referenced to COM. The V_O and I_O parameters are referenced to COM and are applicable to the respective output leads: HO or LO.

Symbol	Definition	Min.	Typ.	Max.	Units	Test Conditions
V_{IH}	Logic "1" (HIN) & Logic "0" ($\overline{LIN}$) input voltage	2.5	—	—	V	$V_{CC} = 10$ V to 20 V
V_{IL}	Logic "0" (HIN) & Logic "1" ($\overline{LIN}$) input voltage	—	—	0.8		
V_{OH}	High level output voltage, $V_{BIAS} - V_O$	—	0.05	0.2		$I_O = 2$ mA
V_{OL}	Low level output voltage, V_O	—	0.02	0.1		
I_{LK}	Offset supply leakage current	—	—	50	μ A	$V_B = V_S = 600$ V
I_{QBS}	Quiescent V_{BS} supply current	—	30	55		$V_{IN} = 0$ V or 5 V
I_{QCC}	Quiescent V_{CC} supply current	—	150	270		$HIN = 5$ V, $\overline{LIN} = 0$ V
I_{IN+}	Logic "1" input bias current	—	3	10		$HIN = 0$ V, $\overline{LIN} = 5$ V
I_{IN-}	Logic "0" input bias current	—	—	1		
V_{CCUV+}	V_{CC} supply undervoltage positive going threshold	8	8.9	9.8	V	
V_{CCUV-}	V_{CC} supply undervoltage negative going threshold	7.4	8.2	9		
I_{O+}	Output high short circuit pulsed current	130	290	—	mA	$V_O = 0$ V, $V_{IN} = V_{IH}$ $PW \leq 10$ μ s
I_{O-}	Output low short circuit pulsed current	270	600	—		$V_O = 15$ V, $V_{IN} = V_{IL}$ $PW \leq 10$ μ s

Functional Block Diagram



Lead Definitions

Symbol	Description
HIN	Logic input for high side gate driver output (HO), in phase
$\overline{\text{LIN}}$	Logic input for low side gate driver output (LO), out of phase
VB	High side floating supply
HO	High side gate drive output
VS	High side floating supply return
VCC	Low side and logic fixed supply
LO	Low side gate drive output
COM	Low side return

Lead Assignments

8 Lead PDIP	8 Lead SOIC
IRS2103PbF	IRS2103SPbF




Figure 1. Input/Output Timing Diagram





Figure 2. Switching Time Waveform Definitions




Figure 3. Deadtime Waveform Definitions




Figure 4A. Turn-On Time vs. Temperature




Figure 4B. Turn-On Time vs. Supply Voltage




Figure 4C. Turn-On Time vs. Input Voltage




Figure 5A. Turn-Off Time vs. Temperature




Figure 5B. Turn-Off Time vs. Supply Voltage




Figure 5C. Turn-Off Time vs. Input Voltage




Figure 6A. Turn-On Rise Time vs. Temperature




Figure 6B. Turn-On Rise Time vs. Voltage




Figure 7A. Turn-Off Fall Time vs. Temperature




Figure 7B. Turn-Off Fall Time vs. Voltage




Figure 8A. Deadtime vs. Temperature




Figure 8B. Deadtime vs. Voltage




Figure 9A. Logic "1" Input Voltage vs. Temperature




Figure 9B. Logic "1" Input Voltage vs. Supply Voltage




Figure 10A. Logic "0" (HIN) & Logic "1" (LIN) Input Voltage vs. Temperature




Figure 10B. Logic "0" (HIN) & Logic "1" (LIN) Input Voltage vs. Voltage




Figure 11A. High Level Output Voltage vs. Temperature




Figure 11B. High Level Output Voltage vs. Supply Voltage




Figure 12A. Low Level Output Voltage vs. Temperature




Figure 12B. Low Level Output Voltage vs. Supply Voltage




Figure 13A. Offset Supply Current vs. Temperature




Figure 13B. Offset Supply Current vs. Voltage




Figure 14A. V_{BS} Supply Current vs. Temperature




Figure 14B. V_{BS} Supply Current vs. Voltage




Figure 15A. Vcc Supply Current vs. Temperature




Figure 15B. Vcc Supply Current vs. Voltage




Figure 16A. Logic "1" Input Current vs. Temperature




Figure 16B. Logic "1" Input Current vs. Voltage




Figure 17A. Logic "0" Input Current vs. Temperature




Figure 17B. Logic "0" Input Current vs. Voltage




Figure 18A. Vcc Undervoltage Threshold(+) vs. Temperature




Figure 18B. Vcc Undervoltage Threshold (-) vs. Temperature




Figure 19A. Output Source Current vs. Temperature




Figure 19B. Output Source Current vs. Supply Voltage




Figure 20A. Output Sink Current vs. Temperature







Figure 20B. Output Sink Current vs. Supply Voltage

Case Outlines




Tape & Reel 8-lead SOIC



CARRIER TAPE DIMENSION FOR 8SOICN


Code	Metric		Imperial	
	Min	Max	Min	Max
A	7.90	8.10	0.311	0.318
B	3.90	4.10	0.153	0.161
C	11.70	12.30	0.46	0.484
D	5.45	5.55	0.214	0.218
E	6.30	6.50	0.248	0.255
F	5.10	5.30	0.200	0.208
G	1.50	n/a	0.059	n/a
H	1.50	1.60	0.059	0.062



REEL DIMENSIONS FOR 8SOICN

Code	Metric		Imperial	
	Min	Max	Min	Max
A	329.60	330.25	12.976	13.001
B	20.95	21.45	0.824	0.844
C	12.80	13.20	0.503	0.519
D	1.95	2.45	0.767	0.096
E	98.00	102.00	3.858	4.015
F	n/a	18.40	n/a	0.724
G	14.50	17.10	0.570	0.673
H	12.40	14.40	0.488	0.566

LEADFREE PART MARKING INFORMATION



ORDER INFORMATION

8-Lead PDIP IRS2103PbF
 8-Lead SOIC IRS2103SPbF
 8-Lead SOIC Tape & Reel IRS2103STRPbF