


## DIMENSIONS: mm



## SPECIFICATIONS

- Primary voltage: 120VAC 60Hz 19W
- Exciting current, open circuit: 50mA max.
- DC resistance  $\pm 15\%$ :  $27\Omega$
- Secondary, no load voltage: 16.8VDC
- Loaded voltage: 12VDC @ 800mA
- DC resistance  $\pm 20\%$ :  $0.8\Omega$
- Insulation resistance:  $100M\Omega$  @ 500VDC
- Dielectric strength: primary-secondary: 1,500VAC for 1 minute  
primary-core: 1,500VAC for 1 minute  
secondary-core: 500VAC for 1 minute
- Temperature rise: 65°C max. @ rated load
- Cord length: 1850  $\pm$  50mm
- Cable: 22AWG X 2C

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.