




HONEYWELL PART NUMBER
21SM144
PRODUCT CODE TXK4400

REV	DOCUMENT	CHANGED BY	CHECK
6	0038111	PK 20MAY08	ASD



NOTE-
1- MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX. DIA. ON .375^{±.002} CENTERS.
2- TERMINALS ARE PLATED FOR SOLDERING.
3- SWITCH WILL WITHSTAND TEMPERATURE OF 250°F.

RELEASE NO.	SR - 7570
REPLACES	-

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± TWO PLACE .XX ± THREE PLACE .XXX ± FOUR PLACE .XXXX ± ANGLES ±		DRAWN	VK	17OCT07	Honeywell			
OPERATING FORCE — — — — 3 OZ MAX		CONTACT ARRANGEMENT SPDT					CHECK	RJ	17OCT07				
RELEASE FORCE— — — — — 1 OZ MIN		30 VOLTS DC RATING			0.030 0.015 0.005	THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - BASIC				
DIFFERENTIAL TRAVEL— — — .002 MAX			SEA LEVEL	50,000 FT									
OVERTRAVEL — — — — — .005 MIN		MAXIMUM INRUSH 24 AMP				INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME		REV
		INDUCTIVE	3 AMP	2.5 AMP					B	I	21SM144		6
		RESISTIVE	5 AMP	5 AMP	THIRD ANGLE PROJECTION 								
		APPROVALS								RASTER		SCALE	-
		KEMA, CE	5A, 250V ~ T85 1E4  										
		UL, CSA	5A, 250 VAC  										