


SPECIFICATION CONTROL DRAWING



Product Revision	Product Name	Component Dimensions				“GA” Wire Gauge (AWG)	Cable Dimensions				
		L max	ØA min	ØB min	ØC min		ØD	ØE	ØF min	G±0.5 (G±0.02)	M±0.5 (M±0.02)
B-020-20-N	D	32.0 (1.260)	6.30 (0.250)	4.60 (0.180)	2.80 (0.110)	20	2.40 (0.095)	2.30 (0.090)	0.30 (0.012)	19.0 (0.750)	6.0 (0.235)
	B-020-22-N						to 6.30 (0.250)	to 4.60 (0.180)			
	B-020-24-N						22				
	B-020-26-N						24				


MATERIALS

1. & 6. INSULATION SLEEVE: Heat-shrinkable, radiation cross-linked modified polyvinylidene fluoride. Transparent blue.
2. & 5. SOLDER PREFORMS WITH FLUX:
 - SOLDER: TYPE Sn63 per ANSI J-STD-006.
 - FLUX: TYPE ROL1 per ANSI J-STD-004.
- 3., 4. & 7. MELTABLE RINGS: Thermally stabilized thermoplastic.
8. CONDUCTOR LEAD: MIL-W-22759/32-GA-9, AWG “GA” (see table). ETFE insulated, stranded tin plated copper.
Color: white.
9. GROUND LEAD: MIL-W-22759/32-GA-6, AWG “GA” (see table). ETFE insulated, stranded tin plated copper.
Color: blue.

APPLICATION

1. The parts covered by this SCD are for use in terminating the primary conductor and the braided shield of a coaxial cable having tin or silver plated conductor and shield, rated for at least 125°C and meeting the dimensional requirements listed.
2. Parts will meet the requirements of Raychem Specification RT-1404 when installed per Raychem RPIP-500-03.
3. Temperature range: -55°C to +150°C.

For best results, prepare
the cable as shown:



	TE Connectivity 305 Constitution Drive Menlo Park, CA 94025, USA	Raychem Products	TITLE: COAXIAL SOLDER SLEEVE DEVICE WITH PRE-INSTALLED STRANDED WIRES			
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. INCHES DIMENSIONS ARE BETWEEN BRACKETS.			DOCUMENT NO.: B-020-GA-N			
TOLERANCES: 0.00 N/A 0.0 N/A 0 N/A	ANGLES: N/A ROUGHNESS IN MICRON	TE Connectivity reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application.		DATE: 15-Apr-11	DOC ISSUE: 2	
DRAWN BY: M. FORONDA	REPLACES: B020xyn1	PROD. REV. SEE TABLE	DCR NUMBER: D000432	SCALE: None	SIZE: A	SHEET: 1 of 1

Print Date: 6-May-11 If this document is printed it becomes uncontrolled. Check for the latest revision.