

4		3		2		1																																		
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		LOC		DIST		REVISIONS																																
© COPYRIGHT - By -		ALL RIGHTS RESERVED.		G		14		P		LTR		DESCRIPTION		DATE		DWN		APVD																						
										L2		REVISED PER ECO-11-004820		11MAR11		RK		HMR																						
AMP WIRE RANGE 12-10 SOLID OR STRANDED UL E13288 12-10 SOLID OR STRANDED SR LR7189 Certified 12-10 SOLID OR STRANDED SERRATIONS WIRE STOP INSULATION BODY AMP AMP AMP A 29.46 MAX [1.160] 1. WIRE INSUL DIA, 3.81-5.84 [.150-.230]																																								
<table><tr><td>-</td><td>-</td><td>-</td></tr><tr><td>25</td><td>LOOSE PIECE, BAG</td><td>8-34072-5</td></tr><tr><td>5</td><td>LOOSE PIECE, BLS</td><td>8-34072-4</td></tr><tr><td>100</td><td>LOOSE PIECE, BOX</td><td>8-34072-1</td></tr><tr><td>1500</td><td>ON TAPE, REEL</td><td>2-34072-2</td></tr><tr><td>500</td><td>LOOSE PIECE</td><td>34072</td></tr><tr><td>QTY</td><td>PACKAGE TYPE</td><td>PART NO</td></tr></table>																				-	-	-	25	LOOSE PIECE, BAG	8-34072-5	5	LOOSE PIECE, BLS	8-34072-4	100	LOOSE PIECE, BOX	8-34072-1	1500	ON TAPE, REEL	2-34072-2	500	LOOSE PIECE	34072	QTY	PACKAGE TYPE	PART NO
-	-	-																																						
25	LOOSE PIECE, BAG	8-34072-5																																						
5	LOOSE PIECE, BLS	8-34072-4																																						
100	LOOSE PIECE, BOX	8-34072-1																																						
1500	ON TAPE, REEL	2-34072-2																																						
500	LOOSE PIECE	34072																																						
QTY	PACKAGE TYPE	PART NO																																						
AMP INCORPORATED CUSTOMER SERVICE SYSTEM				MAX RECOMMENDED OPERATING TEMPERATURE: 90° C [194° F]				THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN M ELLIS 19JUL95		TE Connectivity SPLICE, BUTT, PLASTI-GRIP™ WIRE SIZE,12-10 AWG																										
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: 600V MAX 1000V (FIXTURES OR SIGNS)		DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK C PRESNELL 19JUL95		APVD S BORTNER 19JUL95								NAME																				
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 2.62mm²-6.64mm² [5180-13100]				0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC UL486A		APPLICATION SPEC		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO																				
FOR ORDER ENTRY		1-800-526-5142				MATERIAL BODY, CU ASTM B 152 SLV, PVC, COLOR, YELLO		FINISH TIN PLATE PER MIL-T-10727		WEIGHT -		A3		00779		C-34072		-																						
CUSTOMER DRAWING										SCALE 4:1		SHEET 1 OF 1		REV L2																										