


Series: PJ006




Series options:

F = Flanged

K = Keyed (available only on 8 position)






4P4C






PC Board Layout

6P2C
6P4C
6P6C




PC Board Layout

8P8C



PC Board Layout



Specifications

Phone Jack Series:

PJ

Ratings:	
Current	1.5A
Dielectric strength	1000V RMS for 1 minute
Contact resistance	20mΩ max.
Insulation resistance	500MΩ min.
Spring wire durability	500 mating cycles min.
Operating temperature	-25°C / +90°C
Material:	
Plastic	PBT, Glass-filled UL94V-0
Color	Black
Spring wire	0.45mm Dia., Phosphor Bronze Gold plated over Nickel

ORDERING PROCEDURE

1 - 2 3 4 - 5

- 1) Series
- 2) Number of Positions (# P)
- 3) Number of Contacts (# C)
- 4) Plating:

- 1 = Full Flash Gold
- 2 = Full 10μ Gold
- 3 = Full 30μ Gold
- 4 = Full 50μ Gold

- 5) Series options:

- B = Ferrite Bead (only available on PJ031)
- F = Flanged
- S = Shield
- K = Keyed
- H = Shorting Bar (available only on PJ008, 8 position)