




8

7

6

5

4

3

2

1

TE Connectivity. All Rights Reserved.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—	SEE SHEET 1	—	—	—

3	99.06[3.900]	39	102.01[4.016]	104.14[4.100]	1.27[.050]	40	7—1888291—4
2	99.06[3.900]	39	102.01[4.016]	104.14[4.100]	1.27[.050]	40	7—1888291—3
3	96.52[3.800]	38	99.47[3.916]	101.60[4.000]	0.00[.000]	39	7—1888291—2
2	96.52[3.800]	38	99.47[3.916]	101.60[4.000]	0.00[.000]	39	7—1888291—1
3	93.98[3.700]	37	96.93[3.816]	99.06[3.900]	1.27[.050]	38	7—1888291—0
2	93.98[3.700]	37	96.93[3.816]	99.06[3.900]	1.27[.050]	38	6—1888291—9
3	91.44[3.600]	36	94.39[3.716]	96.52[3.800]	0.00[.000]	37	6—1888291—8
2	91.44[3.600]	36	94.39[3.716]	96.52[3.800]	0.00[.000]	37	6—1888291—7
3	88.90[3.500]	35	91.85[3.616]	93.98[3.700]	1.27[.050]	36	6—1888291—6
2	88.90[3.500]	35	91.85[3.616]	93.98[3.700]	1.27[.050]	36	6—1888291—5
3	86.36[3.400]	34	89.31[3.516]	91.44[3.600]	0.00[.000]	35	6—1888291—4
2	86.36[3.400]	34	89.31[3.516]	91.44[3.600]	0.00[.000]	35	6—1888291—3
3	83.82[3.300]	33	86.77[3.416]	88.90[3.500]	1.27[.050]	34	6—1888291—2
2	83.82[3.300]	33	86.77[3.416]	88.90[3.500]	1.27[.050]	34	6—1888291—1
3	81.28[3.200]	32	84.23[3.316]	86.36[3.400]	0.00[.000]	33	6—1888291—0
2	81.28[3.200]	32	84.23[3.316]	86.36[3.400]	0.00[.000]	33	5—1888291—9
3	78.74[3.100]	31	81.69[3.216]	83.82[3.300]	1.27[.050]	32	5—1888291—8
2	78.74[3.100]	31	81.69[3.216]	83.82[3.300]	1.27[.050]	32	5—1888291—7
3	76.20[3.000]	30	79.15[3.116]	81.28[3.200]	0.00[.000]	31	5—1888291—6
2	76.20[3.000]	30	79.15[3.116]	81.28[3.200]	0.00[.000]	31	5—1888291—5
3	73.66[2.900]	29	76.61[3.016]	78.74[3.100]	1.27[.050]	30	5—1888291—4
2	73.66[2.900]	29	76.61[3.016]	78.74[3.100]	1.27[.050]	30	5—1888291—3
3	71.12[2.800]	28	74.07[2.916]	76.20[3.000]	0.00[.000]	29	5—1888291—2
2	71.12[2.800]	28	74.07[2.916]	76.20[3.000]	0.00[.000]	29	5—1888291—1
3	68.58[2.700]	27	71.53[2.816]	73.66[2.900]	1.27[.050]	28	5—1888291—0
2	68.58[2.700]	27	71.53[2.816]	73.66[2.900]	1.27[.050]	28	4—1888291—9
3	66.04[2.600]	26	68.99[2.716]	71.12[2.800]	0.00[.000]	27	4—1888291—8
2	66.04[2.600]	26	68.99[2.716]	71.12[2.800]	0.00[.000]	27	4—1888291—7
3	63.50[2.500]	25	66.45[2.616]	68.58[2.700]	1.27[.050]	26	4—1888291—6
2	63.50[2.500]	25	66.45[2.616]	68.58[2.700]	1.27[.050]	26	4—1888291—5
3	60.96[2.400]	24	63.91[2.516]	66.04[2.600]	0.00[.000]	25	4—1888291—4
2	60.96[2.400]	24	63.91[2.516]	66.04[2.600]	0.00[.000]	25	4—1888291—3
3	58.42[2.300]	23	61.37[2.416]	63.50[2.500]	1.27[.050]	24	4—1888291—2
2	58.42[2.300]	23	61.37[2.416]	63.50[2.500]	1.27[.050]	24	4—1888291—1
FINISH	DIM Z	DIM Y	DIM X	DIM W	DIM V	NUMBER OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

0. PLC ± —

1. PLC ± —

2. PLC ± 0.13(.005)

3. PLC ± —

4. PLC ± —

ANGLES ± —

MATERIAL —

DWN D. MCMASTER

CHK D. GORENC

APVD D. GORENC

PRODUCT SPEC —

APPLICATION SPEC —

WEIGHT —

OBJUNOE

OBJUNOE

OBJUNOE

OBJUNOE

OBJUNOE

—

TE Connectivity Ltd.

NAME

HEADER ASSY, VERTICAL, SINGLE ROW, FLEXPAC

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A1007791888291—

CUSTOMER DRAWING

SCALE 6:1

SHEET 2 OF 2

REV B1

OBSOLETE

4805 (1/15)