


Module I/O Series



MIO-6250 3 Fast Ethernet Ports



MIO-6250

3 10/100 Mbps with by-pass Ethernet Ports

Features

- 3 x 10/100 Mbps Fast Ethernet
- By-Pass in Port 2 and Port 3
- MIO (Module I/O) Interface

Specifications

- **Chipset** 3 x RealTek® RTL8139
- **Speed** 10/100 Mbps
- **Interface** 3 x RJ45
- **Standard** IEEE 802.3 u (100Base-T) Compatible
- **By-Pass** Ethernet By-Pass in Port 2 and Port 3
- **Dimension** 102 x 85 mm, 4.7" x 3.3"
- **Environment** 0 ~ 60° C, operation
- **Operating Humidity** 0% ~ 90% relative humidity, non-condensing


Ordering Information

- MIO-6250-00A1E

MIO base board: PCM-9380, PCM-9386

MIO-6251 2 mini PCI, Audio, MDC

NEW



MIO-6251

MIO module with 2-slot mini PCI, Audio, MDC

Features

- 2-slot mini PCI device
- 1 Audio (by cable)
- 1 MDC (Mobile Daughter Card) interface (Optional)

Specifications

- **2-slot mini PCI**
- **Data Bus** 32-bit data bus
(compliant with PCI Bus Specification 2.1)
- **PCI Interface** 3.3 V interface (5 V tolerant)
- **mini PCI slot** 2 mini PCI type III A slot
- **Audio** Supports AC97 Audio stereo sound (by cable with MIO base board)
Audio cable P/N# 1700002102
Audio Output Speaker-Out, Line-In, Mic-In
- **MDC (Mobile Daughter Card) Interface** Optional
- **Dimension** 102 x 85 mm, 4.7" x 3.3"
- **Environment** 0 ~ 60° C, operation
- **Operating Humidity** 10% ~ 90% relative humidity, non-condensing

Ordering Information

- MIO-6251-00A1E


MIO base board: PCM-9380, PCM-9386

Module I/O Series



MIO-6253 4 COMs

NEW



MIO-6253

4 COMs MIO Module

Features

- 3 serial ports supports RS-232/422/485 by BIOS
- MIO (Module I/O) Interface

Specifications


- **Chipset** SMSC SCH-3114 LPC I/O with Multiple Serial Ports Controller
- **Serial Port** 3 x D-Sub connector serial RS-232/422/485 Ports and 1 x box header (share with internal M2M port for wireless)
- **Dimension** 102 x 146 mm, 4.7" x 5.7"
- **Environment** 0 ~ 60° C, operation
- **Operating Humidity** 0% ~ 90% relative humidity, non-condensing

Ordering Information

- MIO-6253-00A1E

MIO base board: PCM-9380, PCM-9386

MIO-6254 DVI, TV, Audio



MIO-6254

Audio/DVI/TV-Out MIO Module

Features

- Line-In, Speaker-Out, Mic-In
- MIO DVO to DVI interface
- TV-Out/S-Video
- MIO (Module I/O) interface

Specifications


- **Audio** AC97 Codec Realtek ALC202, Chromtel CH7009A
- **Audio Output** Dual Channel 6W Stereo Audio Speaker-Out, Line-In, Mic-In
- **Video Output** DVI, TV-Out, S-Video
- **Dimension** 102 x 146 mm, 4.7" x 5.7"
- **Environment** 0 ~ 60° C, operation
- **Operating Humidity** 0% ~ 90% relative humidity, non-condensing

Ordering Information

- MIO-6254-00A1E

MIO base board: PCM-9380, PCM-9386

MIO-6255 2 Cardbus



MIO-6255

MIO Module with 2-slot Cardbus

Features

- Complies with PC Card 95/97/98, Card-32 (32 bit), PCMCIA V2.1/JEIDA4.2 (16 bit)
- Supports 2 x PCMCIA slots, accepts type I/II/III PCMCIA Cards
- MIO (Module I/O) interface

Specifications


- Chipset** Richo® R5C486 Cardbus controller
- 2 Cardbus slot** Accepts type I/II/III PCMCIA Card. When type III Card is used in slot 2, the slot 1 will be occupied.
- 16-bit Legacy Mode** YES (3E0/3E2 I/O port) support
- Data Bus** 32-bit data bus
(Compliant with PCI Bus Specification 2.1)
- PCI Interface** 3.3V interface (5 V tolerant)
- Dimension** 102 x 185 mm, 4.7" x 3.3"
- Environment** 0 ~ 60° C, operation
- Operating Humidity** 10% ~ 90% relative humidity, non-condensing

Ordering Information

- MIO-6255-00A1E

MIO base board: PCM-9380, PCM-9386

MIO-6260 1 LAN, 2 COM, 4 USB



MIO-6260

Multi I/O Module with 1 LAN, 2 COM, 4 USB

Features

- 1 x 10/100 Mbps Fast Ethernet
- 4 x USB 2.0 ports
- 2 x RS-232/422/485 interfaces
- Cableless
- MIO (Module I/O) interface

Specifications

- Chipset** Intel 82551ER (MIO-6260L)
NEC uD720101 PCI USB 2.0 controller
SMSC SCH-3114 LPC I/O with Multiple Serial Ports Controller
- I/O Interface** 1x RJ-45 (MIO-6260L), 2 x USB connector,
2 x box header, 2 x RS-232/422/485 by D-Sub connector
Serial ports jumperless, with auto flow control
- Standard** USB 2.0 compliant
IEEE 802.3u 100 Base-T Fast Ethernet Compatible
- Dimension** 102 x 146 mm, 4.02" x 5.75"
- Environment** 0 ~ 60° C, operation
- Operating Humidity** 10% ~ 90% relative humidity, non-condensing

Ordering Information

- MIO-6260-00A1E** MIO module with 2 COM, 4 USB
- MIO-6260L-00A1E** MIO module with 1 LAN, 2 COM, 4 USB

MIO base board: PCM-9380, PCM-9386