

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

76020-4054

Status:

Active

Overview:


GbX I-Trac™ Backplane Connector System

Description:

1.85mm by 3.70mm Pitch, GbX I-Trac™ Right Angle Receptacle Module, Right Guide 7 Row with ESD Clip, 6 Columns, 84 Circuits

Replacement Part Number:

760205054



Documents:

Drawing (PDF)

Product Specification PS-75710-999 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E29179
General	
Product Family	Backplane Connectors
Series	76020
Application	Coplanar, Daughtercard
Component Type	PCB Receptacle
Overview	GbX I-Trac™ Backplane Connector System
Product Name	GbX I-Trac™
Replacement Part Number	760205054
Style	N/A
UPC	883906601416

Physical	
Circuits (Loaded)	84
Circuits (maximum)	84
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	Yes
Keying to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	8.801/g
Number of Columns	6
Number of Pairs	4, Open Pin Field
Number of Rows	7
Orientation	Right Angle
PC Tail Length	2.00mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	1.85mm, 3.70mm
Pitch - Termination Interface	1.00mm, 2.70mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to PCB	Yes
Stackable	No
Surface Mount Compatible (SMC)	Yes

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

76020Series

Mates With

76015 GbX I-Trac™ Vertical Header Module. 76011 GbX I-Trac™ Right Angle Header Module

Use With

78234 GbX I-Trac™ Right Angle Power Header. 76153 Pirate Cannon Wide Guide Module

Application Tooling FAQ	
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.	
Global	
Description	Product #
Daughter Card	0622023000
Signal Module	
Removal Tool	

Temperature Range - Operating	-55°C to +80°C	Press-In Tool	<u>0622018610</u>
Termination Interface: Style	Through Hole - Compliant Pin	for Right Angle	
Electrical		Receptacle and	
Current - Maximum per Contact	1A	Header 7-Row, 4-	
Data Rate	12.0 Gbps	Column	
Real Signals (per 25mm)	48		
Shield Type	N/A		
Shielded	No		
Voltage - Maximum	120V AC (RMS)/DC		
Material Info			
Reference - Drawing Numbers			
Product Specification	PS-75710-999		
Sales Drawing	SD-76020-004		

This document was generated on 03/13/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION