


## PHOTO


# ULTRA

# Ultra 123


## Lithium/Manganese Dioxide

 $\text{Li/MnO}_2$ 

<b>Nominal Voltage:</b>	3.0 V
<b>Typical Voltage:</b>	3.2-3.3 V
<b>Nominal Internal Impedance:</b>	0.25 ohm @ 1kHz
<b>Average Weight:</b>	17.0 gm
<b>Volume:</b>	7.18 cm <sup>3</sup>
<b>Terminals:</b>	Flat, Recessed Negative Terminal, Nickel Plated Steel
<b>Operating Temperature Range:</b>	-20°C to 75°C (-4°F to 167°F)
<b>ANSI:</b> <b>IEC:</b>	5018LC CR17345



## Duracell Ultra 123 Typical Performance



\* Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy / service life that the battery will provide for various load conditions.

This data is subject to change. Performance information is typical. Contact Duracell for the latest information.