


Identification, colors & marks
Cross section

Components

ID	Quantity	Part number	Description
A	15	55A6088-CO1	
B	1	FIL-11-0.050	Cross-linked ETFE Filler 0.050" nom
C	1	FIL-11-0.070	Cross-linked ETFE Filler 0.070 OD

Cable

Outer	Description	Thickness		OD	
		Inches	mm	Inches	mm
Layer 2				0.339	8.61
Shield	Round tinned copper 36 awg regular	0.011	0.27	0.360	9.14
Jacket	Thermorad HT white	0.009	0.23	0.378	9.60
Cable OD tolerance				+ 0.019	+ 0.48

Specification Raychem SPEC 55A

Weight 121.69 lb/kft 181.43 Kg/Km

© 2008 Tyco Electronics Corporation. All rights reserved.

Continued

Physical properties

Jacket tensile strength	5000 psi minimum
Jacket elongation	50% minimum
Jacket Wall	.008 inch minimum

Environmental properties

Accelerated Aging	300 ± 3°C for 7 hours
Voltage Withstand	(Post Environmental) 1000 volts (rms), 60 Hz. 1 minute

Electrical properties

Voltage withstand (dielectric)	1500 volts (rms) conductor to conductor and shield 500 volts (rms) shield to shield when applicable per WC 27500. Coax Components to their own SCD
Jacket Flaws	Impulse Dielectric Test: 6 kV (peak)
Capacitance (maximum)	Conductor to shield: per Spec 1200 Other conductors floating - 38 pF/ft Other conductors to shield - 46 pF/ft Other conductor to guard - 24 pF/ft

Notes

Colors	Colors and color code designators shall be in accordance with MIL-STD-681.
Dimensions	Dimensions are in inches, and unless otherwise designated, are nominal.
Identification, Colors & Marks	The following is the key to the descriptions in the left hand view of the cable on Page 1. Line 1: Identifies the component per the components' ID list. Line 2: Color codes. Line 3: Mark on component "-" mark on component jacket.
Minimum length	Cable will be supplied in 50 ft. minimum lengths unless otherwise specified
Jacket identification	Mark: 55A6088-20-06090.
Marking	Jacket marked in green ink at 6 inch (nom) intervals between marks
Export License Note	The information contained on this drawing may be subject to International Traffic in Arms Regulations (ITAR) or Export Administration Regulations (EAR) controls and may not be disclosed to any foreign person or firm, including foreign persons employed by or associated with your firm, without first complying with all requirements for obtaining an export license if applicable.
Part Number Note	Other codes and suffixes may be added to the Part Number as necessary, to capture any additional requirements imposed by the purchase order
Specification Information	This drawing is the property of Tyco Electronics Corporation and may not be used for any purpose other than for that which it is supplied without the express written authority of Tyco Electronics Corporation.
Trademarks	The TE logo, Tyco Electronics, Raychem and Thermorad are trademarks.