

Technical drawing of a PCB layout showing dimensions and component placement. The drawing includes the following specifications:

- Overall width: 7.812 (with a break symbol indicating it is divided into FIVE SECTIONS).
- Section width: 1.562 (with a tolerance of $\pm .015$).
- Internal section width: 1.312 (with a tolerance of $\pm .010$).
- Section gap: .250 TYP.
- Vertical spacing: 1.000 (with a tolerance of $\pm .015$) and .750 (with a tolerance of $\pm .010$).
- Vertical spacing: .125 (with a tolerance of $\pm .015$).
- Vertical spacing: .218 TYP.
- Vertical spacing: .218 TYP.
- Vertical spacing: .062 DIA. HOLE (TYP. 20 PLS).
- Vertical spacing: 1533-2 TERMINAL MOUNTED INTO .067 DIA. HOLE (TYP. 50 PLS).
- Vertical spacing: SCORE BOTH SIDES (TYP. 4 PLS).

ASTORIA, N.Y. 11105-2017

MINIATURE TURRET TERMINAL BOARD

.062 TH'K G-10 GLASS EPOXY

AS NOTED

BOON
UN

5.12.00

LN

1X

DWG NO.	
---------	--

C/M

UNLESS OTHERWISE SPECIFIED

15256

5.5.05

REVISÉD

A

DATE _____

DESCRIPTION

REV.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Keystone Electronics:](#)

[15256](#)