



PRODUCTS

INDUSTRY SOLUTIONS

CAREERS

RESOURCES

CONTACT MOLEX

FIND DISTRIBUTOR

Home: Terminal Blocks >

Part Number: 39515-1408

3.81mm Pitch Eurostyle™ Vertical PCB Header, with Threaded Retention Inserts and Reverse Imprinting, 8 Circuits



Series image - Reference only

Status:
Replacement:**OBsolete**

Contact Molex

Series:
Category:

39515

Terminal Blocks

Go to [Part Detail](#) ▾ [CHECK DISTRIBUTOR INVENTORY](#) [Add to My Parts](#) [Email this page](#)**Mates With Part(s):**Most 3.81mm Pitch Industry Standard Plugs, [39517](#) Vertical Plug with Retention Screws, [39514](#) Horizontal Plug with Retention Screws**Product Environmental Compliance**[EU ELV](#): Product not active[EU RoHS](#): Product not active[EU RoHS Phthalates](#): Product not active[China RoHS](#):[REACH SVHC](#): Product not active[Low-Halogen Status](#): Product not active [EU RoHS Certificate of Compliance \(PDF\)](#) [Multiple Part Product Compliance Statements](#)

EU RoHS, REACH SVHC, & Low-Halogen

[Multiple Part Industry Compliance Documents](#)

*IPC 1752A Class C

*IPC 1752A Class D

*Molex Product Compliance Declaration

Application Tooling**FAQ**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling[Check our list of old tooling that used to be available for this part](#)Questions on Product Environmental Compliance? Email ProductCompliance@molex.comRequest Molex's CMRT from conflictminerals@molex.com**Part Detail**[COLLAPSE ALL](#)

▼ General

Status	Obsolete
Category	Terminal Blocks
Series	39515
Application	N/A
Comments	with Reverse Imprinting
Component Type	PCB Header
Product Name	ESE, Eurostyle™ Pluggable
Type	Euro Block
UPC	822350435710

▼ Physical

Circuits (Loaded)	8
Entry Angle	N/A
Lock to Mating Part	Yes
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.50mm
PCB Thickness - Recommended	2.50mm
Panel Mount	No
Pitch - Mating Interface	3.81mm
Pitch - Termination Interface	3.81mm
Polarized to Mating Part	Yes
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40°C to +105°C
Wire Size AWG	N/A

▼ Electrical

(Please review the Product Specification for specific details.)

Current - Maximum per Contact 8.0A

Voltage - Maximum 300V

▼ Agency Certification

Please find UL Certificates by searching the UL Database using the Molex Series Number.
[Click here to visit the UL Database](#)

UL E48521

PRODUCTS**QUICK LINKS****RESOURCES****STAY CONNECTED**Antennas
Application Tooling
Cable Assemblies
Connected Lighting
Connectors
Copper Flex
Electrical Products
Industrial Automation
Membrane Switches
Optical Solutions
Printed Electronic SolutionsCompany Information
Contact Molex
Cross-Reference
Koch Industries
Industries
Investor Relations
Literature
Molex Racing
Press Room / Press Releases
Product Index
Sitemap
Terms & ConditionsSupply Chain Transparency
Business Continuity
Compliance
ecocare
Feedback | Help
Jobs
Legal | Trademarks
Mobile Site
Supplier Portal
Privacy Policy
Tradeshows