

CASE FINISH	CURRENT (AMPS)	WORKING VOLTAGE				MAXIMUM DC RESISTANCE (OHMS)	MAXIMUM VOLTAGE DROP		MINIMUM CAPACITANCE (uF)	MIN. INSERTION LOSS PER MIL-STD-220 FULL LOAD, +25°C													
		-55°C TO +85°C		-55°C TO +125°C			DC	AC		14	30	50	75	100	150	300	500	1	10	100	1	10	
		AC	DC	AC	DC					KHz	KHz	KHz	KHz	KHz	KHz	KHz	MHz	MHz	MHz	GHz	GHz		
SOLDER	1.0	125<400Hz>	250	125<400Hz>	200	.025	.025	---	0.3	--	--	--	--	14	18	30	--	50	70	70	70	--	

PART MARKING:


51-353-111
SCI DATE CODE

PACKAGE MARKING:

STANDARD

MARKING NOTES:

N/A



SCHEMATIC

MTG. HARDWARE

NOTES:

1) MOUNTING TORQUE NOT TO EXCEED 7lb-in.

										00	REV	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. [MILLIMETERS] DO NOT SCALE.	TOLERANCES UNLESS OTHERWISE SPECIFIED		ERIE, FAIRVIEW PENNSYLVANIA	
										CN. 178542	CHANGE NOTICE NO.		Fract#ns		SPECTRUM CONTROL INC.	
													Dec. .xx±		Dwn KEVERLINE	
													Dec. .xxx±010		Ckd 2-12-97	
													Angles ±0° 30'		Description	
													CODE IDENT. NO.		EMI Filter	
													DLSP2		51-353-111	
															Sheet 1 of 1	

Quality Products From The Specialists In Electro-Magnetic Compatibility