




LOC		DIST		REVISIONS				
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD	
			C	REVISED PER ECO-08-007327	17APR08	BM	WM	



1. THE CONTACT SURFACES OF THE TERMINALS ARE COATED WITH LUBRICANT.
- (2) MATERIAL:
HOUSING AND COVER — POLYPHENYLENE OXIDE (BLACK).
TERMINALS — PHOS BRONZE PLATED WITH EITHER .000030 MINIMUM GOLD PLATE OR GOLD FLASH OVER PALLADIUM NICKEL PLATE, .000030 MIN TOTAL ON MATING SURFACE. GOLD FLASH PLATED ON TERMINATING SIDE. .000050 MINIMUM NICKEL UNDERPLATE OVER ENTIRE TERMINAL.
EMI SHIELD: NICKEL PLATED DIE CASTING.
- (3) COVER SHOWN LOOSE BUT SHIPPED ASSEMBLED.
4. WIRE RANGE: 26 AWG SOLID THRU 30 AWG SOLID AND 28 AWG STRANDED RIBBON CABLE.
- (5) FLAT CABLE SHALL BE FURNISHED BY CUSTOMER.
- (6) MATING FACE CONSISTS OF TWO ROWS OF TERMINALS ON .085 CENTERS. TERMINATING SIDE CONSISTS OF TERMINALS ON .100 CENTERS FOR AN EFFECTIVE .050 TERMINATION.
- (7) PANEL THICKNESS RANGE:
OUTSIDE MOUNTING — .125 MAX.
INSIDE MOUNTING — .062 MAXIMUM.
8. EMI SHIELD SHIPPED LOOSE.
9. FOR MORE INFORMATION REFER TO AMP PRODUCT SPECIFICATION 108-6076 & APPLICATION SPEC 114-6030.

.620	.310	.149	2.085	REAR PANEL MOUNTING	5554348-1
.640	.320	.126	2.000	FRONT PANEL MOUNTING	
DIM D	DIM C	DIM B	DIM A	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MCMASTER CHK W. MILLHIMES APVD W. MILLHIMES	16JAN08 16JAN08 16JAN08	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0. PLC	± .	PRODUCT SPEC	
		1. PLC	± .	108-6076	
		2. PLC	± .	APPLICATION SPEC	
		3. PLC	± .005	114-6030	
		4. PLC	± .		
		ANGLES	± .		
MATERIAL		FINISH		SIZE A1	CAGE CODE 00779
(2)		(2)		DRAWING NO 5554348	RESTRICTED TO —
CUSTOMER DRAWING				SCALE 2:1	SHEET 1 OF 1