




LP 5.00/180




Technical data	VDE	UL	CSA
Rated voltage (V)	250*	300	300
Rated current (A)	25	15	20
Wire size (mm ² /AWG)	4.0	26...12	26...12
*Pollution severity 3 / Overvoltage category III			
Additional technical data see page 58			

Solder pin length4.5 mm

Color	
Poles	Type
2	LP 5.00/2/180
3	LP 5.00/3/180

Accessories	Page
Marking	40
Mounting	46
Miscellaneous	45




Technical data	VDE	UL	CSA
Rated voltage (V)	250*	300	300
Rated current (A)	24	15	20
Wire size (mm ² /AWG)	4.0	26...12	26...12
*Pollution severity 3 / Overvoltage category III			
Additional technical data see page 58			

Solder pin length4.5 mm4.5 mm

Color	
Poles	Type
2	LP1N 5.00/2/90
3	LP1N 5.00/3/90

Attention: Customers are advised to ensure support for LP1N on the printed circuit board.

Accessories	Page
Marking	40
Mounting	-
Miscellaneous	45



Technical data	VDE	UL	CSA
Rated voltage (V)	250*	300	300
Rated current (A)	24	15	20
Wire size (mm ² /AWG)	4.0	26...12	26...12
*Pollution severity 3 / Overvoltage category III			
Additional technical data see page 58			

Solder pin length4.5 mm4.5 mm

Color	
Poles	Type
4	LP2N 5.00/4/90
6	LP2N 5.00/6/90
8	LP2N 5.00/8/90
10	LP2N 5.00/10/90
12	LP2N 5.00/12/90
14	LP2N 5.00/14/90
16	LP2N 5.00/16/90
18	LP2N 5.00/18/90
20	LP2N 5.00/20/90
22	LP2N 5.00/22/90
24	LP2N 5.00/24/90
26	LP2N 5.00/26/90
28	LP2N 5.00/28/90
30	LP2N 5.00/30/90
32	LP2N 5.00/32/90
34	LP2N 5.00/34/90
36	LP2N 5.00/36/90
38	LP2N 5.00/38/90
40	LP2N 5.00/40/90
42	LP2N 5.00/42/90
44	LP2N 5.00/44/90
46	LP2N 5.00/46/90
48	LP2N 5.00/48/90

Accessories	Page
Marking	40
Mounting	46
Miscellaneous	45-46