



Copyright FCI.

D


1

2



3

4

PLATING CONTACT AREA:	
DASH NR:	PERFORMANCE LEVEL
-1Y	TELCORDIA CO
-2Y	OBSCOLETE
-3Y	CUSTOMER SPECIAL
-4Y	OBSCOLETE
-5Y	CUSTOMER SPECIAL
-6Y	TELCORDIA CO
-7Y	CUSTOMER SPECIAL
-8Y	OBSCOLETE
-9Y	TELCORDIA CO
-10Y	TELCORDIA CO
-11Y	OBSCOLETE
-12Y	CUSTOMER SPECIAL
-13Y	TELCORDIA CO
-14Y	OBSCOLETE
-15Y	CUSTOMER SPECIAL



PC BOARD VERSIONS		
PRODUCTNR:	PCB THICKNESS	DIM'A'
89039-X01LF	1.6	2.90
89039-X11LF	2.4	3.53



NOTES:

- 1 BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS FLAME RETARDANT ACC. UL 94-V0
- 2 TERMINAL MATERIAL: PHOSPHOR BRONZE.
- 3 INDICATED HOLES ARE UNPLATED.
- 4 PRODUCT MARKING: PARTNUMBER & BATCH ID.
- 5 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
- 6 THE HOUSING WILL WITHSTAND EXPOSURE TO 260DEGREE PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.
- 7 THE PRODUCT SPECIFICATION GS-12-453.

mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY	projection	title	
ltr	ecn no	dr	date	linear	0.X ± 0.30	0.XX ± 0.15	0.XXX ± 0.05			
H	DG04-0104	CLU	2004-12-23		0.X ± 0.30	0.XX ± 0.15	0.XXX ± 0.05			
J	DG07-0458	CEN	2007-11-15		0.X ± 0.30	0.XX ± 0.15	0.XXX ± 0.05			
K	DG08-0171	TER	2008-08-26		0° ± 2°					
L	NI1-0131	A.ZH	2011-05-09	dr	H.BOUWKNEGT	1993-03-05		MM	product family METRAL size dwg no sheet 1 of 2	
M	ELX-N-004585	A.ZH	2011-07-20	engr	H.BOUWKNEGT	1993-03-05				
N	ELX-N-006420	A.ZH	2011-09-29	chr	J.WINTJES	1993-03-05				
				oppd	H.BOUWKNEGT	1993-03-05	5:1			
sheet		revision N								
index		sheet 1-2								




Copyright FCI.

D

1 2 3 4

PLATING CONTACT AREA:	
DASH NR:	PERFORMANCE LEVEL
-1Y2	TELCORDIA CO
-2Y2	OBSCOLETE
-2Y1	CUSTOMER SPECIAL
-3Y1	OBSCOLETE
-3Y1	CUSTOMER SPECIAL
-3Y1F	TELCORDIA CO
-2Y1F	CUSTOMER SPECIAL
-3Y1F	TELCORDIA CO
-1Y1F	TELCORDIA CO
-3Y1F	CUSTOMER SPECIAL



NOTES:

- 1 BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS FLAME RETARDANT ACC. UL 94-V0
- 2 TERMINAL MATERIAL: PHOSPHOR BRONZE.
- 3 INDICATED HOLES ARE UNPLATED.
- 4 PRODUCT MARKING: PART NUMBER & BATCH ID.
- 5 SET BACK FOR PRESS BLOCK.
- 6 TOP SURFACE OF PRESS BLOCK MAY EXTEND UP TO 0.4MM HIGHER THAN HOUSING. THIS MAY AFFECT THE TAIL LENGTH BEFORE APPLICATION TO A BOARD
- 7 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
- 8 THE HOUSING WILL WITHSTAND EXPOSURE TO 260DEGREE PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.
- 9 THE PRODUCT SPECIFICATION GS-12-453.

PC BOARD VERSIONS		
PRODUCTNR:	PCB THICKNESS	DIM 'A'
89039-X02LF	1.6	2.90
89039-X12LF	2.4	3.53

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	projection	title
ltr	ecn no	dr	date	linear	angles			
N	ELX-N-006420	A.ZH	2011-09-29	0.X ± 0.30	0.XX ± 0.15			RA FEMALE POWER
				0.XXX ± 0.05	0° ± 2°			RECEPTACLE 12mm PRESS PEG
				dr	H.BOUWKNEGT	1993-03-05	MM	
				engr	H.BOUWKNEGT	1993-03-05		
				chr	J.WINTJES	1993-03-05		
				appd	H.BOUWKNEGT	1993-03-05	scale	
							5:1	
				sheet	revision	N	product family	METRAL
				index	sheet	1-2	size	dwg no
							A2	89039
							sheet	2 of 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FCI:

89039-111