








Part Number & Date Code Printing

PC card drilling dimensions(after plating)
(thickness 1.60±0.20mm)

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.21	D09S13B4G*00**	D09S13B6G*00**
15	39.14	33.32	25.18	24.54	D15S13B4G*00**	D15S13B6G*00**
25	53.03	47.04	39.12	38.25	D25S13B4G*00**	D25S13B6G*00**
37	69.32	63.50	55.68	54.71	D37S13B4G*00**	D37S13B6G*00**
Gold flash					0,76 » gold	

LF FOR LEAD FREE

Threaded ØT M3 = I
Threaded ØT 4.40 = V

REQUIREMENTS

Technical characteristics:

Shell: steel tin plated/Zinc Cr3 plated
Insulators: self-extinguishing black polyster, ULclass94V0
Contacts size 20: brass, gold 0.76µ on mating end, bright tin on termination end over nickel on entire contact
Cycles : >500 for plating 6
>200 for plating 4

Harpoons: phosphor bronze, tin plated
Metal plate for electrical continuity: brass, tin plated/Zinc Cr3 plated
Nuts: brass, tin/Zinc Cr3 plated

Electrical characteristics:

max.current rating: 5A
Test voltage: 1000V
Rated voltage: 300V
Contact resistance: ≤15mΩ
Shell resistance: ≤5mΩ
Insulation resistance: ≥5000MΩ

Climatic characteristics:

Operating temperature range: -55°C +125°C

Dimensions:

in accordance with MIL-C-24308

FOR ROHS DETAILS REFER DWG. NO: C01-8646-0000

mat'l. code				surface		tolerance		projection	product family		
—				ISO 1302	ISO 406	ISO 1101	D—SUB				
ltr	ecn no	dr	date	tolerances unless	otherwise specified				title		
C	I05—0124	JS	2005/07/27	angles		±0.1			MM	SOCKET CONNECTOR DELTA—D WITH SCREWLOCK,HARPOON,METAL BRACKET	
D	I06—0074	SK	2006/06/08		linear	±0.1					
E	ELX—I-15413	MP	2013/08/03	±1°		±0.1		scale 1:1			
—	—	—	—	dr	JOHN SLEEBA	1994/08/01		dwg no		sheet 1 of 1	size
—	—	—	—	engr	MITHUN PAUL	2013/08/03		C01—8646—0292		A3	5
—	—	—	—	chr	MITHUN PAUL	2013/08/03					
—	—	—	—	appd	BIJU K PAUL	2013/08/03					
sheet index		revision sheet		E							
				1							