


FO-80378-003
DRAWN
GLH 17 AUG 73
CHECK
73
LSD 21 AUG 73
CHECK
73
RASTER
17 AUG 73
DRAWN
GLH 17 AUG 73
CHECK
73
LSD 21 AUG 73
CHECK
73
REVISIONS
B 202714
CSL
3 APR 01
A CO-94413
JJA
8 OCT 99
ISSUE
14
M
DRAWING NUMBER
2TP12-70
PAGE 1 OF 1
RELEASE NO. PR-3537
REPLACES




**MICRO SWITCH**
FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL
FED MFG CODE 91929

**SWITCH-TOGGLE
FLUSH KEY**

CATALOG LISTING
2TP12-70



CIRCUIT DIAGRAM

LUG SIDE (MOMENTARY POSITION)	CENTER (MAINTAINED POSITION)	OPPOSITE LUG (MOMENTARY POSITION)
		

L192 10A 125, 250, 277 VAC
1/4HP 125 VAC,
1/2HP 250, 277 VAC
3A 125 VAC "L"



- NOTES
- 1 - MICRO SWITCH CATALOG LISTING MARKED ON SIDE OF SWITCH
 - 2 - SCREWS FURNISHED UNASSEMBLED

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.									
ELECTRICAL DATA									
MILITARY RATING (AMPS)									
CONTINUOUS	RESISTIVE LOAD				LAMP LOAD		INDUCTIVE LOAD		
	30	115	250	115	250	30 VDC	115 VAC	30 VDC	115 VAC
UNLESS OTHERWISE NOTED DIMENSIONS ARE IN INCHES TOLERANCES ARE: ONE PLACE () ± .030 TWO PLACE () ± .015 THREE PLACE () ± .005 ANGLES ±									
WEIGHT									

SCALE FULL
DO NOT SCALE PRINT