

n-Channel Power MOSFET

OptiMOS™
BSB056N10NN3 G

Data Sheet

2.5, 2011-05-27
Final

Industrial & Multimarket


1 Description

OptiMOS™ 100V products are class leading power MOSFETs for highest power density and energy efficient solutions. Ultra low gate- and output charges together with lowest on state resistance in small footprint packages make OptiMOS™ 100V the best choice for the demanding requirements of voltage regulator solutions in Solar, Drives, Datacom and Telecom applications. Super fast switching Control FETs together with low EMI Sync FETs provide solutions that are easy to design in. OptiMOS™ products are available in high performance packages to tackle your most challenging applications giving full flexibility in optimizing space- efficiency and cost.



Features

- Optimized for high switching frequency DC/DC converter
- Excellent $Q_g \times R_{DS(on)}$ product (FOM)
- Very low on-resistance $R_{DS(on)}$
- Pb-free plating; RoHS compliant
- Halogen-free according to IEC61249-2-21
- Double sided cooling
- Compatible with DirectFET® package MN footprint and outline
- Low parasitic inductance
- Low profile (<0.7 mm)



Applications

- Synchronous rectification
- Primary side switches
- Power management for high performance computing
- High power density point of load converters



Table 1 Key Performance Parameters

Parameter	Value	Unit	Related Links
V_{DS}	100	V	IFX OptiMOS webpage IFX OptiMOS product brief IFX OptiMOS spice models IFX Design tools
$R_{DS(on),max}$	5.6	mΩ	
I_D	83	A	
Q_{OSS}	73	nC	
$Q_{g,typ}$	56		

Type	Package	Marking
BSB056N10NN3 G	MG-WDSO-2	0110

2 Maximum ratings

at $T_j = 25\text{ °C}$, unless otherwise specified.

Table 2 Maximum ratings

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Continuous drain current	I_D	-	-	83	A	$V_{GS}=10\text{ V}, T_C=25\text{ °C}$
				52		$V_{GS}=10\text{ V}, T_C=100\text{ °C}$
				9		$V_{GS}=10\text{ V}, T_A=25\text{ °C}, R_{thJA}=45\text{ K/W})^{1)}$
Pulsed drain current ²⁾	$I_{D,pulse}$	-	-	332		$T_C=25\text{ °C}$
Avalanche energy, single pulse	E_{AS}	-	-	450	mJ	$I_D=30\text{ A}, R_{GS}=25\text{ }\Omega$
Gate source voltage	V_{GS}	-20	-	20	V	
Power dissipation	P_{tot}	-	-	78	W	$T_C=25\text{ °C}$
				2.8		$T_A=25\text{ °C}, R_{thJA}=45^{1)})\text{ K/W}$
Operating and storage temperature	T_j, T_{stg}	-40	-	150	°C	
IEC climatic category; DIN IEC 68-1		55/150/56				

1) Device on 40 mm x 40 mm x 1.5 mm epoxy PCB FR4 with 6cm² (one layer, 70 µm thick) copper area for drain connection. PCB is vertical in still air.

2) See figure 3 for more detailed information

3 Thermal characteristics

Table 3 Thermal characteristics

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Thermal resistance, junction - case	R_{thJC}	-	-	1.6	K/W	top
		-	1	-		bottom
Device on PCB	R_{thJA}	-	-	45		6 cm ² cooling area ¹⁾

1) Device on 40 mm x 40 mm x 1.5 mm epoxy PCB FR4 with 6 cm² (one layer, 70µ, thick) copper area for drain conneciton. PCB is vertical in still air.

4 Electrical characteristics

Electrical characteristics, at $T_j=25\text{ °C}$, unless otherwise specified.

Table 4 Static characteristics

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Drain-source breakdown voltage	$V_{(BR)DSS}$	100	-	-	V	$V_{GS}=0\text{ V}$, $I_D=1\text{ mA}$
Gate threshold voltage	$V_{GS(th)}$	2	2.7	3.5		$V_{DS}=V_{GS}$, $I_D=100\text{ }\mu\text{A}$
Zero gate voltage drain current	I_{DSS}	-	0.1	10	μA	$V_{DS}=100\text{ V}$, $V_{GS}=0\text{ V}$, $T_j=25\text{ °C}$
		-	10	100		$V_{DS}=100\text{ V}$, $V_{GS}=0\text{ V}$, $T_j=125\text{ °C}$
Gate-source leakage current	I_{GSS}	-	10	100	nA	$V_{GS}=20\text{ V}$, $V_{DS}=0\text{ V}$
Drain-source on-state resistance	$R_{DS(on)}$	-	5	5.6	$\text{m}\Omega$	$V_{GS}=10\text{ V}$, $I_D=30\text{ A}$
			6.2	8.1		$V_{GS}=6\text{ V}$, $I_D=15\text{ A}$
Gate resistance	R_G	-	0.5	-	Ω	
Transconductance	g_{fs}	34	69		S	$ V_{DS} >2 I_{D} R_{DS(on)max}$, $I_D=30\text{ A}$

Table 5 Dynamic characteristics

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Input capacitance	C_{iss}	-	4100	5500	pF	$V_{GS}=0\text{ V}$, $V_{DS}=50\text{ V}$, $f=1\text{ MHz}$
Output capacitance	C_{oss}	-	750	1000		
Reverse transfer capacitance	C_{rss}	-	27	-		
Turn-on delay time	$t_{d(on)}$	-	15	-	ns	$V_{DD}=50\text{ V}$, $V_{GS}=10\text{ V}$, $I_D=30\text{ A}$, $R_G=1.6\text{ }\Omega$
Rise time	t_r	-	9	-		
Turn-off delay time	$t_{d(off)}$	-	25	-		
Fall time	t_f	-	8	-		

Table 6 Gate charge characteristics¹⁾

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Gate to source charge	Q_{gs}	-	17	-	nC	$V_{DD}=50\text{ V}$, $I_D=30\text{ A}$, $V_{GS}=0\text{ to }10\text{ V}$
	Q_{gd}		9.7			
Gate to drain charge	Q_{sw}	-	20	-		
Switching charge	Q_g	-	56	74		
Gate charge total	$V_{plateau}$	-	4.2	-	V	
Output charge	Q_{oss}		73	97	nC	$V_{DD}=50\text{ V}$, $V_{GS}=0\text{ V}$

1) See figure 16 for gate charge parameter definition

Table 7 Reverse diode characteristics

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Diode continuous forward current	I_s			65	A	$T_C=25\text{ °C}$
Diode pulse current	$I_{S,pulse}$			316		
Diode forward voltage	V_{SD}	-	0.9	1.2	V	$V_{GS}=0\text{ V}$, $I_F=I_S$, $T_j=25\text{ °C}$
Reverse recovery charge	Q_{rr}	-	174	-	nC	$V_R=50\text{ V}$, $I_F=30\text{ A}$, $di_F/dt=100\text{ A}/\mu\text{s}$
Reverse recovery time	t_{rr}	-	64	-	ns	

5 Electrical characteristics diagrams

Table 8



1 Power dissipation	2 Drain current
 $P_{\text{tot}} = f(T_c)$	 $I_D = f(T_c)$; parameter: V_{GS}

Table 9



3 Safe operating area $T_c = 25\text{ °C}$	4 Max. transient thermal impedance
 $I_D = f(V_{DS})$; $T_J = 25\text{ °C}$; $D = 0$; parameter: T_p	 $Z_{(thJC)} = f(t_p)$; parameter: $D = t_p / T$

Table 10



5 Typ. output characteristics $T_c=25\text{ °C}$	6 Typ. drain-source on-state resistance
	
$I_D=f(V_{DS}); T_J=25\text{ °C}; \text{parameter: } V_{GS}$	$R_{DS(on)}=f(I_D); T_J=25\text{ °C}; \text{parameter: } V_{GS}$

Table 11



7 Typ. transfer characteristics	8 Typ. forward transconductance
	
$I_D=f(V_{GS}); V_{DS} >2 I_D R_{DS(on)max}$	$g_{fs}=f(I_D); T_J=25\text{ °C}$

Table 12



9 Drain-source on-state resistance	10 Typ. gate threshold voltage
	
$R_{DS(on)} = f(T_j); I_D = 30 \text{ A}; V_{GS} = 10 \text{ V}$	$V_{GS(th)} = f(T_j); V_{GS} = V_{DS};$

Table 13



11 Typ. capacitances	12 Forward characteristics of reverse diode
	
$C = f(V_{DS}); V_{GS} = 0 \text{ V}; f = 1 \text{ MHz}$	$I_F = f(V_{SD}); \text{parameter: } T_j$

Table 14





13 Avalanche characteristics	14 Typ. gate charge
 $I_{AS}=f(t_{AV})$; $R_{GS}=25\ \Omega$; parameter: $T_{J(start)}$	 $V_{GS}=f(Q_{gate})$; $I_D=30\text{ A pulsed}$; parameter: V_{DD}

Table 15

15 Drain-source breakdown voltage	16 Gate charge waveforms
 $V_{BR(DSS)}=f(T_J)$; $I_D=1\text{ mA}$	

6 Package outlines




Figure 1 Outlines MG-WDSO-2, dimensions in mm/inches

7 Package outlines






Figure 2 Outlines MG-WDSO-2, dimensions in mm/inches

8 Package outlines



9 Package outlines



9 Revision History

Revision History: 2011-05-27, 2.5

Previous Revision:

Revision	Subjects (major changes since last revision)
0.1	Release of target data sheet
2.0	Release of Final data sheet
2.3	Package outlines errata corrections
2.4	DirectFET Disclaimer expired

We Listen to Your Comments

Any information within this document that you feel is wrong, unclear or missing at all?

Your feedback will help us to continuously improve the quality of this document.

Please send your proposal (including a reference to this document) to: erratum@infineon.com



Edition 2011-05-27

Published by

Infineon Technologies AG

81726 Munich, Germany

© 2011 Infineon Technologies AG

All Rights Reserved.

Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

Information

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (www.infineon.com).

Warnings

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.

The Infineon Technologies component described in this Data Sheet may be used in life-support devices or systems and/or automotive, aviation and aerospace applications or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support, automotive, aviation and aerospace device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered..