





PART NO.
20021111



RECOMMENDED PCB LAYOUT

SCALE 5.000

NOTES:

- 1.MATERIAL:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC, UL94-V0 BLACK.
TERMINAL: COPPER ALLOY
- 2.THE HOUSING WILL WITHSTAND EXPOSURE TO 260~C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER OR VAPOR PHASE REFLOW OVEN.
- 3.THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- 4.PRODUCT SPEC: GS-12-629
- 5.PACKAGE SPEC: GS-14-1420

mat'l. code				surface	tolerance	projection	product family			
				ISO 1302 ✓	ISO 406 ISO 1101	mm	MINITEK127®			
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title			
E	ELX-N-23548	TIM	03/21/16	angles	linear	.0±.30	UNSHROUDED HDR VT TH			
F	ELX-N-25883	TONY	01/11/17			.00±.20				
G	ELX-N-27768	TONY	08/18/17	0°±2'		.000±.10	scale 1:1			
				dr	ZK HU	09/28/12	Amphenol FCI	dwg no		sheet 1 of 2
				enr	ZK HU	09/28/12		20021111		size A3
				chr	BIAN RICK	09/28/12		type Product Customer Drawing		
				appd	BIAN RICK	09/28/12				
sheet index	revision sheet	G 1	G 2							

PART NO.	POS.	DIM"X"	DIM"Y"
20021111-XXX92XXLF	2 X 46	58.42	57.15
20021111-XXX94XXLF	2 X 47	59.69	58.42
20021111-XXX96XXLF	2 X 48	60.96	59.69
20021111-XXX98XXLF	2 X 49	62.23	60.96
20021111-XXXA0XXLF	2 X 50	63.50	62.23

```

-LEAD FREE
-PLATING OPTIONAL
1: GOLD FLASH AT CONTACT, 127um MIN. MATTE TIN AT TAIL
2: GOLD FLASH AT CONTACT, GOLD FLASH AT TAIL
4: 0.25um Au MIN. AT CONTACT, 127um MIN.MATTE TIN AT TAIL
5: 0.25um Au MIN. AT CONTACT, GOLD FLASH AT TAIL
6: 0.38um GXT MIN. AT CONTACT, 127um MIN.MATTE TIN AT TAIL
7: 0.38um GXT MIN. AT CONTACT, GOLD FLASH AT TAIL
8: 0.76um GXT MIN. AT CONTACT, 127um MIN.MATTE TIN AT TAIL
9: 0.76um GXT MIN. AT CONTACT, GOLD FLASH AT TAIL

```

- PACKING STYLE
 - T: TUBE
 - Q: TAPE & REEL WITHOUT CAP
- PIN NO. SEE TABLE
- MATING LENGTH(DIM"A")
 - 0: 3.05MM
- TAIL LENGTH(DIM"B")
 - 0: 2.30MM (FOR 1.6MM PCB)
 - 1: 1.60MM (FOR 1.0MM PCB)
 - 2: 2.70MM (FOR 2.0MM PCB)
- RESERVE CODE
 - 0: STANDARD

mat'l. code					surface ISO 1302 ✓			tolerance ISO 406 ISO 1101			projection 		product family MINITEK127®										
ltr ecn no dr date					tolerances unless otherwise specified			angles linear		.0±.30				title UNSHROUDED HDR VT TH									
								.00±.20															
					0°±2'					.000±.10		scale 1:1		dwg no sheet2 of 2 size A3 20021111									
					dr ZK HU 09/28/12																		
					engr ZK HU 09/28/12																		
					chr BIAN RICK 09/28/12																		
					appd BIAN RICK 09/28/12									type Product Customer Drawing									
sheet index		revision sheet		G 1	G 2																		