








PC board drilling dimensions(after plating)
(thickness ≤ 3.20±0.30mm)



LEAD FREE PART NUMBERS

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P90C4P*00LF	D09P90C6P*00LF	D09P90C8P*00LF
15	39.14	33.32	25.18	25.12	19.18	D15P90C4P*00LF	D15P90C6P*00LF	D15P90C8P*00LF
25	53.03	47.04	39.12	38.84	33.12	D25P90C4P*00LF	D25P90C6P*00LF	D25P90C8P*00LF
37	69.32	63.50	55.68	55.30	49.68	D37P90C4P*00LF	D37P90C6P*00LF	D37P90C8P*00LF
						Gold Flash	0.76µ Gold	1.25µ Gold

Threaded ØT M3 = L
Threaded ØT 4.40 = X

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0001

Notes:

- The nut can protrude above the surface of insulator but maintaining the footprint dimension 5.60±0.15 mm.

mat'l. code	surface	tolerance	projection	product family
-	ISO 1302	ISO 406 ISO 1101	MM	D-SUB
ltr	ecn no	dr	date	title
F	ELX-I-21256	AB	2015/07/14	MALE CONNECTOR DELTA-D STRAIGHT - PRESS FIT
				dwg no
				sheet 1 of 1
				size
				A3
				type
				Product Customer Drawing
sheet index	revision	F		
	sheet	1		