



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		D	REVISED PER ECR-13-011489	14DEC2013	KH	PD



SUGGESTED MATING TAB



- 1 MATL: #2 HARD BRASS OR NICKEL PLATE STEEL.
- 2 NO BURRS PERMISSIBLE AT HOLE.
- 3 TIN PLATING IS REQUIRED ON BRASS WHEN TERMINAL TEMPERATURE IS OVER 225° F.
- 4 MUST BE FLAT WITHIN 0.076[.003] OVER THIS LENGTH.
- 5 HOLE MUST BE SYMMETRICAL ABOUT TAB $\pm$ WITHIN 0.076[.003].
- * TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.



- 1 CONTINUOUS STRIP ON REELS.
- 2 ACCEPTS [#18-#14] SINGLE WIRE SIZES AND COMBINATION OF TWO [#18'S]. WIRE CRIMP IS 3.05 [0.120], F TYPE.
- 3 FITS INSULATION RANGE OF 3.81-5.08 [0.150-0.200] DIA OR TWO WIRES AT 2.79 [0.110] MAX DIA. INSULATION CRIMP IS 5.59 [0.220], F TYPE.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 9/17/98		 TE Connectivity			
		CHK MS FEHER 9/17/98					
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
		APVD E HOWARD 9/17/98		RECEPTACLE, POSITIVE-LOCK, MARK III, 4.75 [.187] SERIES			
		PRODUCT SPEC —					
		APPLICATION SPEC —					
		WEIGHT —					
MATERIAL BRASS		FINISH SEE TABLE		SIZE A2	CAGE CODE 00779	DRAWING NO C=1217114	RESTRICTED TO —
CUSTOMER DRAWING				SCALE 6:1	SHEET 1 of 1	REV D	