




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		H1	ECO-05-10198	20MAR06	MB	JLG

$\varnothing$ 0.38[.015] (M)
TYP AT POST TIPS




0.64±0.02
[.025±.001]

$\varnothing$ 0.38[.015] (M)
TYP AT POST TIPS



RECOMMENDED HOLE LAYOUT

- 1
- .00254[.000100] BRIGHT TIN-LEAD OVER .00127[.000050] NICKEL.
- 2
- POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 3
- THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING.
- 4
- ON ASSEMBLIES WITH FOUR OR MORE POSITIONS, TWO POLARIZATION SLOTS.
ON ASSEMBLIES WITH TWO OR THREE POSITIONS, ONE POLARIZATION SLOT.
- 5
- POSITION NOTED FOR REFERENCE ONLY.
- 6
- PRELIMINARY PART-NOT RELEASED FOR PRODUCTION.
- 7
- .00254[.000100] MATTE TIN OVER .00127[.000050] NICKEL.
- 8
- HIGH TEMPERATURE CONFIGURATION
- 9
- STANDOFFS NOT PRESENT ON UNDERSIDE OF ASSEMBLY



6	89	7	16	48.77 [1.920]	50.8 [2.000]	18	19	5-147969-5
	89	7	17	48.77 [1.920]	50.8 [2.000]	18	19	5-147969-4
	89	7	10	28.45 [1.120]	30.48 [1.200]	10	11	5-147969-3
	89	7	19	51.31 [2.020]	53.34 [2.100]	19	20	5-147969-2
	89	7	2	8.13 [.320]	10.16 [.400]	2	3	5-147969-1
6		1	18	51.31 [2.020]	53.34 [2.100]	19	20	147969-6
6		1	16	48.77 [1.920]	50.8 [2.000]	18	19	147969-5
		1	17	48.77 [1.920]	50.8 [2.000]	18	19	147969-4
		1	10	28.45 [1.120]	30.48 [1.200]	10	11	147969-3
		1	19	51.31 [2.020]	53.34 [2.100]	19	20	147969-2
		1	2	8.13 [.320]	10.16 [.400]	2	3	147969-1
	REMARKS	PLATING	POSITIONS OMITTED	C	B	A	NO. OF POSN	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN	R.BROWN	10SEP01	tyco Electronics				Tyco Electronics Corporation Harrisburg, Pa 17105-3608			
				CHK	K.WRIGHT	10SEP01								
				APVD	K.WRIGHT	10SEP01	NAME				HDR ASSY, VERT, SINGLE ROW 2.54[.100] CL, 0.64[.025] SQ POST, WITH PLZN & LATCHING, AMPMODU MTE			
				PRODUCT SPEC			108-25034							
				APPLICATION SPEC			114-25026							
				WEIGHT			-							
				CUSTOMER DRAWING										
				SCALE			4:1							
				SHEET			1 OF 1							
				REV			H1							